




<b>CVC627</b>	4.3mm lens, silver housing
<b>CVC627B</b>	4.3mm lens, black housing
<b>CVC627W</b>	6mm lens, white housing

### Features

- Day & night operation: 20 built-in LEDs controlled by a CDS sensor allow this color camera to see a perfect BW picture in the dark at distances up to 65' (depending on scene reflection)
- Weather resistant: can stand up to any type of weather
- Attractive housing: available in white, black and silver
- IP67 compliant
- 12VDC / 24VAC dual voltage operation
- 5 year warranty



### Specifications

Image Sensor .....	1/3" color CCD
Resolution.....	600 TV lines
Minimum Illumination.....	0.1 lux (LED off), 0 lux (LED on)
Camera Type .....	Weather resistant, day/night capability
Iris .....	Electronic shutter
Electronic Shutter Speed.....	1/60 sec. – 1/100,000 sec.
Effective Pixels .....	768 (H) x 494 (V)
TV Standard .....	NTSC
Synchronization.....	Internal
Scanning System.....	2:1 interlace
Video Output.....	1Vp-p / 75 Ohms
Gamma .....	0.45 typ.
S/N Ratio .....	48dB
Gain Control .....	Automatic
Backlight Compensation.....	Automatic
Effective IR Range.....	65' (depending on scene reflection)
Number of LEDs .....	20
CDS Sensor.....	Yes

Power Consumption .....	120mA (LED off), 420mA (LED on)
Power Supply .....	12VDC / 24VAC dual voltage operation (power supply not included)
Operating Temperature.....	14° F – 120° F
Housing .....	Weather resistant, aluminum, removable/ adjustable sunshield, reflective IR booster
Mount.....	Stainless steel, universal wall / ceiling mount included
Dimensions.....	2.75" (Dia.) x 3.65" (L)
Weight .....	12.5 oz.
Cable .....	5' of power/video cable (CVC627W / CVC627B) 60' of power/video cable (CVC627)
Included in Package .....	DC power pigtail, wall/ceiling mount, installation hardware

### Optional Accessories



Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 8/6/12

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880  
www.specotech.com