

RCM+™ Rack Mounted Horizontal Cable Manager With Cover Plastic Finger Style

- SB870 Series horizontal manager with snap-on removable hinged door opens past 180°, and remains open in up position for convenient cable access.
- #12-24 mounting hardware is included.
- UL Listed as a Communication Circuit Accessory. File No. E171936.
- Material: Steel - 14 ga. (ASTM A569) with UL 94V-0 black plastic components.
- Finishes___: Flat Black Powder Coat (FB) or Silver Powder Coat (SL)
- SX series managers are used with extended depth vertical cable managers on page 92. Features 2.5" (63mm) longer fingers than the standard manager.




SB87019S2FB



Inside Dimensions of Cable Managers

Style	Height (IH)	Depth (ID)
S1	0.7"	5.5"
S2	2.4"	5.5"
S3	4.2"	5.5"
S4	5.9"	5.5"
SX1	0.7"	8.0"
SX2	2.4"	8.0"
SX3	4.2"	8.0"
SX4	5.9"	8.0"



	Catalog Number	Width		Height	Weight	
		In.	(mm)		Lbs.	(kg)
✓	SB87019S1___	19"	(482)	1U	2.1	(0.9)
	SB87023S1___	23"	(584)	1U	2.3	(1.0)
✓	SB87019S2___	19"	(482)	2U	2.5	(1.1)
	SB87023S2___	23"	(584)	2U	2.7	(1.2)
✓	SB87019S3___	19"	(482)	3U	2.8	(1.3)
	SB87023S3___	23"	(584)	3U	3.1	(1.4)
	SB87019S4___	19"	(482)	4U	3.2	(1.4)
	SB87023S4___	23"	(584)	4U	3.6	(1.6)
Extended Fingers						
	SB87019SX1___	19"	(482)	1U	2.4	(1.1)
	SB87019SX2___	19"	(482)	2U	3.1	(1.4)
	SB87019SX3___	19"	(482)	3U	3.8	(1.7)
	SB87019SX4___	19"	(482)	4U	4.4	(2.0)

✓ FB is a popular item