

DL1200-CAT5 - CAT 5E VOICE AND HIGH-SPEED DATA PROTECTED PATCH PANEL

ORDERING INFORMATION

ITW Linx Part Number	Description
DL1200-CAT5	Protects high-performance CAT 5e Outside Plant Cables as well as CAT 5e UTP cables for LAN/Data applications (RJ-45 In & Out). 16 Volts.

* Questions about ordering? Please contact us at **1-800-336-LINX** / Contact an authorized distributor for pricing * (MOQ: 6)

TECHNICAL SPECIFICATIONS

PRODUCT SPECIFICATIONS:

Agency Approval	UL Primary (497) and Isolated Loop (497B)
Grounding Requirements	Field installed solid copper wire
..... #10 AWG for Primary	
..... #14 AWG for Isolated Loop	
Recommended Grounding Impedance	<0.5 Ohm
Width	19"
Height	1.7"
Depth	4.5"
Weight	5.83 lbs
Product Warranty	Lifetime
Connected Equipment Warranty	Up to \$5,000

SIGNAL LINE SURGE PROTECTION: (LAN)

Signal Perfect Circuitry	Yes
Fused	Yes
Performance Rating	Cat 5e
Clamping Level	16V
Response Time	1-5 Nanoseconds
Capacitance	<20pF
Wires Protected	8-wires, 4-pairs per port
Termination Type	RJ-45 In and Out



Features:

- UL Listed for Primary (497) and Isolated Loop (497B) applications
- Exceeds TIA/EIA Standards 568 and 758 for CAT 5e performance
- Solid-state protection provides the fastest response to transient voltages (1-5 nanoseconds) by quickly diverting damaging surges to ground
- Use between buildings in a campus environment as a building entrance protector or in hostile industrial applications as an isolated loop protector
- 12-ports, with replaceable 4-port modules
- RJ45 input to RJ45 output
- Single-height rack mountable chassis (1U)
- **Lifetime Product Warranty** - This surge protector shall be free of any defects in design, materials, or workmanship, or ITW Linx will repair or replace the defective product
- **\$5,000 Connected Equipment** - This ITW Linx product will protect your equipment or we will repair or replace it up to \$5,000

For up-to-date warranty information, please visit our web site at www.itwlinx.com.



Signal Perfect™



RACKMOUNT
PATCH PANEL

DATALINX
SERIES

