



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: TLP606RNET

6 Outlets, 6ft cord, 1440 Joules, 1-line rotating gold coaxial 1-line tel/modem protection - Surge Suppressor

Highlights



- 6 outlets - 4 rotate, 2 standard
- 6 ft cord
- 1440 joules
- 1 line tel/modem and 1-line gold coax (2.2GHz bandwidth) protection
- \$150,000 [Ultimate Lifetime Insurance](#) (USA, Puerto Rico & Canada only)

Description

Tripp Lite's TLP606RNET Surge Suppressor provides high-performance protection--1440 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! 6 outlets - 4 that rotate, 2 that are standard, 1-line coaxial protection - that also rotates and 1-line tel/modem for maximum protection. \$150,000 [Ultimate Lifetime Insurance](#) coverage (USA and Canada only). Includes two diagnostic LEDs, 6 ft. gold coaxial cable, 6ft network cable and 6 ft. phone cord.

Applications

- Perfect for small home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more

Package Includes

- TLP606RNET Surge Suppressor
- Instruction manual with warranty information
- 6 ft. gold coaxial cable
- 6 ft. phone cord
- 6 ft network cord

Features

- 6 outlets - 4 rotate, 2 standard, allow for easier plug connection and removal
- 1440 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- 6ft cord
- 1 set of surge-protected gold coaxial connectors (with included 6 ft. coaxial cable) safeguard components on cable, satellite or antenna line (2.2GHz bandwidth)
- 1 set of surge-protected tel/modem.ethernet connectors (with included 6 ft. phone cord and 6ft Network cable)
- 2 diagnostic LEDs alert user to protection and grounding status
- High-impact plastic housing (black) stands up to the most demanding environments
- \$150,000 [Ultimate Lifetime Insurance](#) (USA and Canada Only)

Specifications

OVERVIEW	
Intended Application	Home/Office

OUTPUT	
Frequency compatibility	60 Hz
Circuit Breaker (amps)	15
Outlet quantity / type	6 NEMA 5-15R
Outlet orientation	Rotatable
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input connection type	NEMA 5-15P RIGHT ANGLE
Voltage compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Diagnostic LEDs	Built-in LEDs confirm suppressor "protected" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC suppression joule rating	1440
AC suppression response time	< 1 ns
Protection modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Clamping voltage (RMS)	300,500,500
UL1449 let through rating	400, 500, 500
EMI / RFI filtering	150KHZ TO 100MHZ
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line
Network (Ethernet) Protection	Yes
PHYSICAL	
Shipping Dimensions (HWD/in)	12.60 x 6.10 x 2.36
Shipping Dimensions (HWD/cm)	32 x 15.49 x 5.99
Shipping weight (lbs)	1.54
Shipping weight (kg)	0.70
Unit Dimensions (HWD/in)	2.2 x 5.91 x 4.72
Unit Dimensions (HWD/cm)	5.6 x 15 x 12
Unit weight (lbs)	2.22

Unit weight (kg)	1.00
Material of construction	Plastic
Receptacle Color	Black
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
cUL / CSA (Canada)	cUL
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=5493.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.