



Tripp Lite
1111 West 35th Street
Chicago, IL 60609 USA
Telephone: +(773) 869 1234
E-mail: saleshelp@tripplite.com

Model #: PDUH20DV

Single-Phase Basic PDU, 16/20A 100-240V, 1U Horizontal Rackmount, 2 C19 and 12 C13 outlets, C20 inlet, C20 input with L6-20P adapter

Highlights

- Basic single phase 16/20A 100-240V PDU
- 1U horizontal rackmount installation
- C20 input with NEMA L6-20P adapter; 12 ft. / 3.7m line cord
- 2 C19 and 12 C13 outlets
- Reversible housing; 3.75 in. / 9.5cm depth



Description

Tripp Lite Basic Power Distribution Units / PDU systems offer reliable rackmount power distribution. Supplies equipment with continuous power from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

Applications

- Ideal for datacenters, network closets, equipment racks and a wide variety of other application types

Package Includes

- PDUH20DV PDU rackmount PDU
- Owner's manual

Features

- 16/20A single phase 100-240V Basic Power Distribution Unit / PDU (Agency de-rated to 16A continuous)
- C20 inlet with included C19 to C20 input cable, includes L6-20P adapter
- 14 outlets (2 C19, 12 C13)
- 12 ft. / 3.7m line cord
- 1U horizontal rackmount format installs in one rack space
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Reversible housing
- Back panel grounding lug

Specifications

OVERVIEW	
PDU Type	Basic
OUTPUT	
Frequency compatibility	50 / 60 Hz
Output nominal voltage	100-240V

Overload protection	n/a
Outlet quantity / type	2 C19, 12 C13
Outlet Type	IEC-C13, IEC-C19
INPUT	
Nominal Input Voltage(s) Supported	100V AC; 120V AC; 127V AC; 200V AC; 208V AC; 230V AC; 240V AC
PDU Input Voltage	100; 120; 127; 200; 208; 230; 240
Maximum Input Amps (A)	20
Maximum Input Amps (A) Details	20A maximum input (Agency de-rated to 16A continuous)
PDU Plug Type	NEMA L6-20P; IEC-320 C20
Input cord length (ft.)	12
Input cord length (m)	3.7
Input cord details	Input cable is detachable PDU C20 inlet
Voltage compatibility (VAC)	100; 120; 127; 200; 208; 230; 240
Phase	Single-Phase
PHYSICAL	
Shipping Dimensions (HWD/in)	2.25 x 20.5 x 9.5
Shipping Dimensions (HWD/cm)	5.7 x 52.1 x 24.1
Shipping weight (lbs)	5.7
Shipping weight (kg)	2.6
Unit Dimensions (HWD/in)	1.75 (1U) x 17.25 x 3.75
Unit Dimensions (HWD/cm)	4.45 x 43.8 x 9.5
Unit weight (lbs)	3.75
Unit weight (kg)	1.7
Material of construction	Sheet metal
Style	Rackmount, Vertical Rackmount, Wallmount/Under-Counter
Form factors supported	1U rackmount, 0U vertical rackmount, wall-mount, and under-counter installation
PDU Form Factor	Horizontal (1U, 2U, etc)
Outlets center to center measurement	Distance between front (C13) outlets = 28.75mm; Distance between rear (C19) outlets = 55mm; Distance between rear (C13) outlets = 28.75mm
SPECIAL FEATURES	
Appearance	All black color scheme
TVSS grounding	Rear grounding lug
CERTIFICATIONS	

Certifications	Tested to UL 60950 (USA), CSA (Canada), CE (EU), RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

Related Items

Optional Products

Related Model	Description	Qty.
PDUSIDEBRKT	Enables Vertical Installation of Select 1U PDUs, Power Strips and Surge Suppressors in SmartRack Configurations	1
P052-008	8-ft. Power cord (IEC-320-C19 to BS1363 UK Plug)	1
P050-008	8-ft. Power cord (IEC-320-C19 to CEE 7/7 SCHUKO)	1
P047-002	2-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C14)	1
P047-004	4-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C14)	1
P047-006	6-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C14)	1
P047-010	10-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C14)	1
P036-002	2-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C20)	1
P036-006	6-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-C20)	1
P034-010	10-ft. 14AWG Heavy Duty Power cord (IEC-320-C19 to NEMA 5-15P)	1
P049-010	10-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 to NEMA 5-20P)	1
P045-010	10-ft. 12AWG Heavy-Duty Power cord (IEC-320-C19 to NEMA L5-20P)	1
P040-010	10-ft. 12AWG Heavy Duty Power cord (IEC-320-C19 to IEC-320-L6-20P)	1
P002-002	2-ft. Power Cord (IEC-320-C14 to NEMA 5-15R)	1
P005-002	2-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to IEC-320-C14)	1
P005-006	6-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to IEC-320-C14)	1
P005-010	10-ft. Heavy-Duty 14AWG Power cord (IEC-320-C13 to IEC-320-C14)	1
P032-007	7-ft. 12AWG Heavy Duty Power cord (IEC-320- C13 to IEC-320-C20)	1
P070-010	10-ft. IEC309 to C19 Power Cord	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at www.tripplite.com/en/products/model.cfm?txtModelID=4799.

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.