



Technical Specification



RM-CX06-16R



The **RM-CX06-16R** is a 19" rackmount, 16 channel, surge protector ideal for protecting expensive video equipment such as multiplexers from damaging transients coming from exposed video lines. This device utilizes a three-stage hybrid topology to clamp over-voltage transients and mitigate damaging sneak currents.

Features

* 16 Channel Three-Stage Series Hybrid

* Low Insertion Loss

* Sneak / Fault Current Protection

* Shielded Case

Specifications

Clamping Voltage

6 Volts

Insertion Loss

0.1db @ 10MHz (typical)

Characteristic Impedance

75 Ohms

Connectors

BNC-Type

Frequency Range

0 to 20MHz

Peak surge Current

20kA @ 8 X 20 μ s

Response Time

<1ns

Dimensions

1.75H x 19W x 2.0D (1U)

Temperature

-40°C to + 85°C