

## Stainless Steel Wallplates

### APPLICATION

Leviton's single-gang and dual-gang Stainless Steel Wallplates offer field-configurable flexibility, and accept QuickPort® snap-in connectors and adapters to support a variety of commercial and residential applications. Available in several port configurations; the single-gang wallplate comes in 1-, 2-, 3-, 4- or 6-ports, and the dual-gang version comes in 2-, 4-, 6-, 8- or 12-ports. Use different colored QuickPort connectors and adapters for easy port identification.

### STANDARDS COMPLIANCE

Meets or exceeds all applicable standards: cULus Listed; complies with TIA/EIA-568-B; and meets FCC Part 68.

### PHYSICAL SPECIFICATIONS

Dimensions: Single-gang: 4.5"H x 2.75"W x .45"D  
Dual-gang: 4.5"H x 4.56"W x .45"D  
Capacity: Single-gang: 1-, 2-, 3-, 4- or 6-port versions  
Dual-gang: 2-, 4-, 6-, 8- or 12-port versions  
Materials: Type 302 stainless steel

### DESIGN CONSIDERATIONS

- To identify ports, use different colored connectors and adapters for each application.


### UNIQUE FEATURES

- Compatible with all individual QuickPort connectors and adapters
- Fits standard NEMA electrical boxes
- Individual-port configurability allows specification flexibility
- Brushed stainless steel finish

### WARRANTY INFORMATION

For a copy of Leviton product warranties, log on to [www.levitonvoicedata.com/warranty](http://www.levitonvoicedata.com/warranty).

See ELECTRONIC FILES for CAD files (.DXF, .DWG, MS-DOS.EPS) on disk



Stainless Steel Wallplates

For ELECTRONIC Typical Specs see (.TXT) file on disk.

### TYPICAL SPECIFICATION

Single-gang and dual-gang Stainless Steel Wallplates shall be field-configurable, and accept snap-in connectors and adapters to support commercial and residential applications. The single-gang wallplate shall provide 1-, 2-, 3-, 4- or 6-ports, and the dual-gang wallplate shall provide 2-, 4-, 6-, 8- or 12-ports. Each wallplate shall have a brushed stainless steel finish, fit standard NEMA electrical boxes, be cULus Listed, and compliant with FCC Part 68, and TIA/EIA-568-B specifications.



For Technical Support Call 1-425-485-4288; in USA call 1-800-824-3005.  
Spec sheets and updates are also available at [www.levitonvoicedata.com](http://www.levitonvoicedata.com).

2222 - 222nd St. SE • Bothell, WA 98021 USA  
Tel: 1-800-722-2082 / 1-425-485-4288 • Fax: 1-425-483-5270 • Int'l Fax: 1-425-485-9170 • GSA Schedule Available



# Stainless Steel Wallplates


**Part Numbers**  
**43080-xSx**  
**43080-S12**

.....



## DIMENSIONAL LINE ART

See ELECTRONIC FILES for CAD images  
 (.DXF, .DWG, MS-DOS.EPS)

### Single-Gang Wallplate



### Dual-Gang Wallplate



## PART NUMBERS

<b>Stainless Steel Wallplates</b>	<b>Part No.</b>
1-Port Single-Gang Wallplate	43080-1S1
2-Port Single-Gang Wallplate	43080-1S2
3-Port Single-Gang Wallplate	43080-1S3
4-Port Single-Gang Wallplate	43080-1S4
6-Port Single-Gang Wallplate	43080-1S6
2-Port Dual-Gang Wallplate	43080-2S2
4-Port Dual-Gang Wallplate	43080-2S4
6-Port Dual-Gang Wallplate	43080-2S6
8-Port Dual-Gang Wallplate	43080-2S8
12-Port Dual-Gang Wallplate	43080-S12

For Technical Support Call 1-425-485-4288; in USA call 1-800-824-3005.  
 Spec sheets and updates are also available at [www.levitonvoicedata.com](http://www.levitonvoicedata.com).



2222 - 222nd St. SE • Bothell, WA 98021 USA • Tel: 1-800-722-2082 / 1-425-485-4288 • Fax: 1-425-483-5270 • Int'l Fax: 1-425-485-9170 • GSA Schedule Available

