

## QuickPort® Field-Configurable Recessed-Angled Patch Panel

### APPLICATION

Leviton's QuickPort Recessed-Angled Patch Panel features a customizable design for fiber and copper applications, accepting all QuickPort Snap-in Modules for optimum rack density on industry standard racks. The panel features a dual-angle design to easily route cables into vertical cable managers, reducing the need for horizontal, front cable management bars.



### SPECIFICATION

QuickPort Recessed-Angled Patch Panel shall feature a 24-, 48-, or 72-port dual-angle design for industry standard equipment racks. It shall be UL Listed, CSA Certified, comply with TIA-568-C.2 standards and meet FCC Part 68. The panel shall accept all QuickPort modules and feature white write-on front labels.

### FEATURES

- Improved accessibility brings termination field closer to installer for easier termination
- Low profile provides more aisle space in closets
- Unique dual-angle design reduces cable bend radius and keeps terminations within a standard 3" depth rack

### DESIGN CONSIDERATIONS

- Mounts on industry standard 19" wide equipment racks
- Accepts all QuickPort Snap-in Modules for copper and fiber applications
- Write-on blocks and port numbers are silk-screened in white

### STANDARDS COMPLIANCE

Meets or exceeds all applicable standards:

UL Listed  
CSA Certified  
Complies with TIA-568-C.2  
Meets FCC Part 68

### PHYSICAL SPECIFICATIONS

Dimensions: 24-port: 1.72"H x 19"W x 4.08"D  
48-port: 3.50"H x 19"W x 4.08"D  
72-port: 3.50"H x 19"W x 4.08"D

Capacity: 24-port, 48-port, 72-port  
Materials: 16-gauge steel  
Mounting: 19" rack-mount  
Color: Painted black with white silk-screening


### WARRANTY INFORMATION

For warranty information, go to [leviton.com/lcp](http://leviton.com/lcp) or call 800.722.2072.


**ELECTRONIC FILES**

For CAD files, typical specs, or technical drawings (.DXF, .DWG, Visio), visit [www.leviton.com](http://www.leviton.com).


**4W256-H24**



**4W256-H48**



**4W256-D72**



4W256-\*\*\*

**PART NUMBERS**

Description	Part No.
1RU 24-Port QuickPort Recessed-Angled Panel	4W256-H24
2RU 48-Port QuickPort Recessed-Angled Panel	4W256-H48
2RU 72-Port QuickPort Recessed-Angled Panel	4W256-D72

