

ENATS* 09-6 Issue 8

Multipair LSZH Insulated and Sheathed - Armoured, Un-screened



Application

These light current control cables are primarily for use with control, indication and alarm equipment for switchgear and similar power apparatus in power stations and substations. Suitable for use on circuits where the nominal voltage does not exceed 150 V d.c. or 110 V a.c.

Specification

- Generally in accordance with ENATS 09-6 Issue 8 Table E.3B
- **Conductors:** Solid (Class 1) plain copper conductors to BS EN 60228
- **Insulation:** Polythene insulation Type 03 to BS6234
- **Pair Identification:** See colour code chart 4 on page 4:50
- **Binder Tape:** p.e.t.p. tape of suitable overlap
- **Inner Sheath:** LSF inner sheath Type LTS1 or LTS3 to BS7655
- Mild galvanised steel wires to BS EN 10257-1
- **Outer Sheath:** Black LSF outer sheath Type LTS1 or LTS3 to BS7655. In addition, the LSF outer sheath displays following characteristics:
 - Minimum oxygen index: 30%
 - Maximum HCL Emission @ 800°C: 0.5%
- Flame retardant to BS EN 60332-3-24 & IEC60332-3-24 Category C (NMV1.5)
- **Voltage Rating:** 150 V d.c./110 V a.c.
- **Temperature Rating:** 70°C maximum conductor operating temperature

* ESI standards are now covered under ENATS (Energy Network Association Technical Specification). Standard number remains same, i.e. ENATS 09-6.

Anixter Number	Number of Pairs	Nominal Cond Area	Nominal Cond Stranding	Insulation Thickness	Nominal Diameter Under Armour	Armour Wire Diameter	Nominal O/D	Approx Cable Weight	Minimum Bending Radius (fixed bend)
		mm ²	#/mm	mm	mm	mm	mm	kg/km	mm
A11BP-P002LSF	2PR(QD)	0.50	1/0.8	0.30	5.10	0.90	9.50	197	60
A11BP-P005LSF	5PR	0.50	1/0.8	0.30	8.50	0.90	13.10	279	80
A11BP-P010LSF	10PR	0.50	1/0.8	0.30	10.90	1.25	16.40	526	100
A11BP-P020LSF	20PR	0.50	1/0.8	0.30	14.40	1.25	20.10	740	130
A11BP-P030LSF	30PR	0.50	1/0.8	0.30	18.60	1.60	25.20	880	160
A11BP-P040LSF	40PR	0.50	1/0.8	0.30	22.90	1.60	29.70	1345	180
A11BP-P050LSF	50PR	0.50	1/0.8	0.30	23.80	1.60	31.80	1700	200
A11BP-P060LSF	60PR	0.50	1/0.8	0.30	25.90	1.60	33.10	1810	200

(QD) = Quad

For further technical information refer to page 4:50.

Non-armoured versions also available.

Details upon request.

Technical Information for ENATS* 09-6 Issue 8

PAIR IDENTIFICATION

Pairs will be identified as given in colour code chart 4 below:

COLOUR CODE CHART 4

Pair Number	Colour	
	Wire a	Wire b
1	White	Blue
2	White	Orange
3	White	Green
4	White	Brown
5	White	Grey
6	Red	Blue
7	Red	Orange
8	Red	Green
9	Red	Brown
10	Red	Grey
11	Black	Blue
12	Black	Orange
13	Black	Green
14	Black	Brown
15	Black	Grey
16	Yellow	Blue
17	Yellow	Orange
18	Yellow	Green
19	Yellow	Brown
20	Yellow	Grey

2-pair cables are laid up in quad formation in order of rotation: white, red, blue, orange.

Cables having 40-pairs and above are laid up in 20-pair units, each individual 20-pair unit having pair identification as per colour code chart 4. Each unit shall be identified by a numbered tape applied directly on to the unit binder tapes or by a separate longitudinal tape applied under a clear unit binder tape. The numbers shall run from 1 upwards in units of 1.

Technical Information for ENATS* 09-6 Issue 8

ELECTRICAL CHARACTERISTICS**Conductor Resistance**

Maximum d.c. conductor resistance @ 20°C (LOOP) 136 ohms/km.

Insulation Resistance

Minimum insulation resistance @ 20°C 50 Mohms/km.

Mutual Capacitance

Maximum mutual capacitance 125nF/km (@ 1kHz) PVC insulation.

Capacitance Unbalance

Maximum capacitance unbalance:

2-pair 800pF for 500m of cable @ 1kHz.

above 2-pair 400pF for 500m of cable @ 1kHz.

Mutual Inductance

Maximum mutual inductance 1000 μ H for 500m of cable @1kHz.

* ESI standards are now covered under ENATS (Energy Network Association Technical Specification). Standard number remains same, i.e. ENATS 09-6.

1
2
3
4
5
6
7
8
9
10
11
12
13
14
15
16
17
18
19
20