


Single Unit Distribution

OFNR/OFNP



Flame Retardant PVC Jacket

Buffered Optical Fiber

Central Strength Member

Dielectric Aramid Strength Members

SPECIFICATIONS

6-12 Fiber Configuration	Flexible 900 µm tight buffered fibers, dielectric aramid yarns and overall jacket
18-24 Fiber Configuration	Band marked flexible 900 µm tight buffered fibers, dielectric aramid yarns, overall jacket and central strength element
Jacket	OFNR: Flame retardant (FR) PVC OFNP: FR, low smoke PVC
Performance Compliance	UL 1651 CSA C22.2 No. 232 UL 1666 NFPA 262 Telcordia GR-409, Issue 1 Telcordia GR-409, Issue 2 ANSI/ICEA S-83-596 ANSI/TIA-568-C.3 RoHS-compliant
NRTL Programs	UL, c(UL) Listed OFNR UL, c(UL) Listed OFNP

PRODUCT DESCRIPTION

These Superior Essex premises distribution optical fiber cables are constructed using a single unit - single jacket RoHS-compliant design with fiber counts from 6 through 24. The design consists of flexible 900 µm tight buffered industry standard 250 µm fibers (900/250/125 µm) and is suitable for use with standard connectors, like the SC, ST, and FC, and small-form-factor connectors like the LC. Dielectric aramid yarns are applied for strength while maintaining flexibility. The 18 and 24-fiber cable designs have a flexible glass reinforced central strength element for added durability and performance. A durable, flame resistant outer jacket is applied over the cable core using appropriate OFNR or OFNP rated materials.

APPLICATIONS

- Intra-building backbones
- Conduit pathways
- Service entrance to communication closets
- "Behind-the-shelf" connections

FEATURES

- Marked in feet and meters

BENEFITS

- Meets commercial, government and international requirements for length markings

ENVIRONMENTAL SPECIFICATIONS

	Riser	Plenum
Operation	-20°C to +75°C	0°C to +75°C
Storage/Shipping	-40°C to +75°C	-40°C to +75°C
Installation	-20°C to +65°C	0°C to +65°C

PART NUMBERS AND PHYSICAL CHARACTERISTICS

Listing	Part Number ¹	Fiber Type	Fiber Count	Nominal Diameter in (mm)	Nominal Weight lbs/kft (kg/km)	Maximum Tensile Loading		Minimum Bend Radius	
						Install lbs (N)	Long Term lbs (N)	Install in (mm)	Long Term in (mm)
OFNR	43006x101	Single mode	6	0.20 (5.0)	17 (25)	150 (660)	45 (200)	3.0 (75)	2.0 (50)
OFNR	43008x101	Single mode	8	0.24 (6.0)	20 (30)	150 (660)	45 (200)	3.5 (90)	2.4 (60)
OFNR	43012x101	Single mode	12	0.26 (6.5)	25 (37)	150 (660)	45 (200)	3.8 (98)	2.6 (65)
OFNR	43018xK01*	Single mode	18	0.30 (7.5)	35 (51)	300 (1,320)	90 (400)	4.4 (113)	3.0 (75)
OFNR	43024xK01*	Single mode	24	0.33 (8.5)	44 (66)	300 (1,320)	90 (400)	5.0 (128)	3.3 (85)
OFNP	44006x101	Single mode	6	0.20 (5.0)	17 (25)	100 (440)	30 (130)	3.0 (75)	2.0 (50)
OFNP	44008x101	Single mode	8	0.21 (5.4)	19 (28)	100 (440)	30 (130)	3.2 (81)	2.1 (54)
OFNP	44012x101	Single mode	12	0.24 (6.2)	24 (35)	100 (440)	30 (130)	3.7 (93)	2.4 (62)
OFNP	44018xK01*	Single mode	18	0.28 (7.0)	33 (49)	150 (660)	45 (200)	4.1 (105)	2.8 (70)
OFNP	44024xK01	Single mode	24	0.31 (7.8)	42 (62)	150 (660)	45 (200)	4.6 (117)	3.1 (78)
OFNR	43006yG01	Multimode	6	0.20 (5.0)	17 (25)	150 (660)	45 (200)	3.0 (75)	2.0 (50)
OFNR	43008yG01	Multimode	8	0.24 (6.0)	20 (30)	150 (660)	45 (200)	3.5 (90)	2.4 (60)
OFNR	43012yG01	Multimode	12	0.26 (6.5)	25 (37)	150 (660)	45 (200)	3.8 (98)	2.6 (65)
OFNR	43018yK01	Multimode	18	0.30 (7.5)	35 (51)	300 (1,320)	90 (400)	4.4 (113)	3.0 (75)
OFNR	43024yK01	Multimode	24	0.33 (8.5)	44 (66)	300 (1,320)	90 (400)	5.0 (128)	3.3 (85)
OFNP	44006yG01	Multimode	6	0.20 (5.0)	17 (25)	100 (440)	30 (130)	3.0 (75)	2.0 (50)
OFNP	44008yG01	Multimode	8	0.21 (5.4)	19 (28)	100 (440)	30 (130)	3.2 (81)	2.1 (54)
OFNP	44012yG01	Multimode	12	0.24 (6.2)	24 (35)	100 (440)	30 (130)	3.7 (93)	2.4 (62)
OFNP	44018yK01	Multimode	18	0.28 (7.0)	33 (49)	150 (660)	45 (200)	4.1 (105)	2.8 (70)
OFNP	44024yK01	Multimode	24	0.31 (7.8)	42 (62)	150 (660)	45 (200)	4.6 (117)	3.1 (78)

¹Only available with TeraFlex® Bend Resistant single mode optical fiber types.

SINGLE MODE OPTICAL FIBER TYPES

	Reduced Water Peak	TeraFlex® Bend Resistant		
		G.657.A1	G.657.A2	G.657.B3
¹ Replace "x" with:	3	K	J	L
Standard Jacket Colors*		Yellow		

MULTIMODE OPTICAL FIBER TYPES

	TeraGain® 62.5/125	TeraGain Laser Optimized 50/125			TeraFlex Bend Resistant Laser Optimized 50/125		
		10G/150	10G/300	10G/550	10G/150	10G/300	10G/550
¹ Replace "y" with:	6	A	B	F	M	N	P
Standard Jacket Colors*	Orange	Aqua					

*Other jacket colors available upon request. See the "Optical Fiber Selection Chart" in the "Technical Information" section for detailed fiber type specifications.