



Anixter Part No : RG59-LSNH-BLK-P100

Part NO. □ 20070615-22

Ver. □ A0


Product Code RG59 LSNH (95% coverage)

Page □ 1 / 1

1.CONSTRUCTION

Item		A.Q.L	Description
Conductor	NO./mm	0.58	Copper clad steel
	0.58	(+/-0.010)	
Insulation	NO./mm	3.70	Solid PE Insulation
	3.70 SPE	(+/-0.18)	
Shield	NO./mm	112 (+/-2)	(95% coverage)
	112 / 0.16	0.16 (+/-0.008)	Bare copper braid shield
Jacket	NO./mm	6.15	LSNH jacket
	6.15	(+/-0.25)	

2.DESIGN



3.CHARACTERISTICS

Item	Description		Standards
1. Cond. Res.	20□, Conductor DC Resistance		< 26.10 Ω/ 100M
2. Insul. Res.	20□, Insulation DC Resistance		> 200 MΩ.M
3. Capacitance	-----		67±5 pF/M
4. Velocity ratio	-----		66.6±3 %
5. Char. Imped.	20□, 200MHz		75±5 Ω
6. Attenuation	20□ -dB/100M □ +/-15%□	100 MHz	11.8
		200 MHz	16.9
		400 MHz	24.5
		800 MHz	36.3
		1000 MHz	40.9

Remark: Please contact us if you have more requirements or specifications subject to change, or else in accordance with the standards.

Prepared: Zhao

Approved by □

Client approved □

Date □ 2007-06-15