

**RFET-24SM-001-75M****Bend Insensitive Singlemode Fiber LC to LC 24-Fiber Cable Assembly with pulling grip, 75 m**

Construction Materials

Fiber Type	Bend insensitive singlemode fiber (G.657.A1)
Total Fibers, quantity	24
Furcation Color	Yellow
Jacket Color	Black

Dimensions

Cord Length	75.0 m 246.1 ft
Breakout Length, Fiber, end 1	1 m 3 ft
Breakout Length, Fiber, end 2	2 m 7 ft

Environmental Specifications

Environmental Space	Riser Wireless installation
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

General Specifications

Construction Type	Breakout
Cable Glands	No glands
Color, connector A	Blue
Color, connector B	Blue
Interface Feature, connector A	Uniboot
Interface Feature, connector B	Uniboot
Interface, connector A	LC
Interface, connector B	LC
Minimum Bend Radius, furcation	30.0 mm 1.2 in
Pulling Grips, quantity	1

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

760135939 | R-024-CN-8F-F12BK — Indoor/Outdoor Single Jacket All-Dielectric Riser Rated Central Tube Cable

- CS-8F-IOLT (Product Component—not orderable) — Low Macrobending, Zero Water Peak, Dispersion-

Product Specifications

COMMScope®

RFFT-24SM-001-75M

Unshifted Singlemode Fiber

