

Cutting & Notching Tools – Journeyman™ Snips

Offset Snips

JOURNEYMAN

Additional Features:

- J2100L, J2101R, J2106S and J2106S snips feature exclusive Klein Kurve® handles for natural hand positioning and ease of use.
- J2106S Journeyman snips cut 20 gauge cold rolled steel and 24 gauge stainless steel, with a 2-3/8" length of cut for faster cutting.
- J2100L, J2101R and J2102S Journeyman snips cut 18 gauge cold rolled steel and 22 gauge stainless steel.




Cat. No.	Cutting Pattern	Snip Type	Cutting Length	Color Code	Overall Length	Cutting Capacity: Cold Rolled/Stainless Steel	Weight (oz.)
J2100L	left/straight	offset	1-1/4" (32 mm)	red/black	9-1/2" (241 mm)	18 gauge/22 gauge	15.5
J2101R	right/straight	offset	1-1/4" (32 mm)	green/black	9-1/2" (241 mm)	18 gauge/22 gauge	15.7
J2102S	straight/wide curves	offset	1-1/2" (38 mm)	yellow/black	9-1/2" (241 mm)	18 gauge/22 gauge	15.5
J2106S	straight/wide curves	long cut offset	2-3/8" (60 mm)	yellow/black	10-1/2" (266 mm)	20 gauge/24 gauge	18.2

Cutting & Notching Tools

Aviation Snips – Regular/Offset/Bulldog

- Forged and heat-treated steel blades for strength and durability.
- Regular and offset blades have the capacity of cutting 18 gauge cold-rolled sheet metal and 22 gauge stainless steel sheet metal.
- Offset blades provide ease of cutting tight curves and keep user's hand away from metal.
- Bulldog snips (Cat. No. 2103) for notching or trimming 16 gauge cold-rolled sheet metal and 18 gauge stainless steel sheet metal.
- Spring-loaded for self-opening action.
- Latch keeps jaws closed when not in use.
- Hardened handles for extra strength.
- Contoured plastic handles are comfortable and color-coded by cutting pattern.



Cat. No.	Cutting Pattern	Snip Type	Cutting Length	Color Code	Overall Length	Cutting Capacity	Weight (oz.)
1100L	left / straight	aviation	1-3/8" (35 mm)	red	9-3/4" (248 mm)	18 ga.	14.4
1101R	right / straight	aviation	1-3/8" (35 mm)	green	9-3/4" (248 mm)	18 ga.	14.7
1102S	straight / wide curve	aviation	1-1/2" (38 mm)	yellow	10-1/8" (257 mm)	18 ga.	14.4
2100L	left / straight	offset	1-1/4" (32 mm)	red	9-1/2" (241 mm)	18 ga.	15.5
2101R	right / straight	offset	1-1/4" (32 mm)	green	9-1/2" (241 mm)	18 ga.	15.7
2102S	straight / wide curve	offset	1-1/2" (38 mm)	yellow	9-1/2" (241 mm)	18 ga.	15.5
2103	notch	bulldog	7/8" (22 mm)	yellow	9-1/4" (235 mm)	16 ga.	13.9

Replacement springs for aviation snips

- P406 replacement spring for Cat. Nos. 1100L and 1102S
- P407 replacement spring for Cat. No. 1101R

All dimensions are in inches and (millimeters).

⚠WARNING: Always wear approved eye protection.

⚠WARNING: Never use on or near live electrical circuits

⚠WARNING: NOT insulated. Will NOT protect against electrical shock.

