


Enterprise Solutions
760009217 | N-008-DS-CM-FSUAG/8W004/5L004
Low Smoke Zero Halogen Riser Distribution Cable, 8 fiber single-unit

Representative Image



General Specifications

Cable Type	Distribution
Construction Type	Non-armored
Subunit Type	Gel-free

Construction Materials

Fiber Type Solution	Composite fiber LazrSPEED® 300, 50 µm multimode fiber (OM3) TeraSPEED®, zero water peak singlemode fiber (G.652.D or G.652.D OS2)
Total Fiber Count	8
Fiber Type	TeraSPEED®, zero water peak singlemode fiber (G.652.D or G.652.D OS2)
Fiber Type, quantity	4
Jacket Color	Aqua
Second Fiber Type	LazrSPEED® 300, 50 µm multimode fiber (OM3)
Second Fiber Type, quantity	4

Dimensions

Cable Weight	18.8 lb/kft 28.0 kg/km
Diameter Over Jacket	5.60 mm 0.22 in

Physical Specifications

Minimum Bend Radius, loaded	8.4 cm 3.3 in
-----------------------------	-----------------

760009217 | N-008-DS-CM-FSUAQ/8W004/5L004

Minimum Bend Radius, unloaded	5.6 cm		2.2 in
Tensile Load, long term, maximum	200 N		45 lbf
Tensile Load, short term, maximum	150 lbf		667 N
Vertical Rise, maximum	500.0 m		1640.4 ft

Flame Test Specifications

Flame Test Listing	NEC OFNR-LS (ETL) and c(ETL)
Flame Test Method	IEC 60332-3 IEC 60754-2 IEC 61034-2 IEEE 383 UL 1666 UL 1685

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH) Riser
Installation Temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Mechanical Test Specifications

Compression	10 N/mm		57 lb/in
Compression Test Method	FOTP-41		IEC 60794-1-2, Section 7
Flex	100 cycles		
Flex Test Method	FOTP-104		IEC 60794-1-2, Section 10
Impact	4.34 ft lb		5.88 N-m
Impact Test Method	FOTP-25		IEC 60794-1-2, Section 8
Strain	See long and short term tensile loads		
Strain Test Method	FOTP-33		IEC 60794-1-2, Section 5
Twist	10 cycles		
Twist Test Method	FOTP-85		IEC 60794-1-2, Section 11

Environmental Test Specifications

Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	Not applicable
Low High Bend	-40 °C to +70 °C (-40 °F to +158 °F)
Low High Bend Test Method	FOTP-28 IEC 60794-1-2, Section 28
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3 IEC 60794-1-2, Section 22

Qualification Specifications

Cable Qualification Standards	ANSI/ICEA S-83-596-2001 Telcordia GR-409-CORE Issue 2
-------------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system



Included Products

CS-5L-TB (Product Component—not orderable) — LazrSPEED® 300 OM3 Multimode Fiber

CS-8W-TB (Product Component—not orderable) — TeraSPEED® Singlemode Fiber