

# Dual Band (2.4 GHz, 5 GHz) Ethernet Bridge/Router

**AirborneM2M™ Enterprise Series** 



#### PRODUCT FEATURES

- 10/100 Mbps to 802.11a/b/g/n (2.4 GHz, 5 GHz)
- Wide operating temperature Range (-20°C to +85°C)
- Compact form factor
- AirborneM2M<sup>™</sup> SpeedLink roaming provides enhanced connection reliability
- Advanced Enterprise Class wireless security (WPA2-Enterprise, WPA, WEP, EAP)
- Available in OEM version (without enclosure)
- Supported by Airborne Management Center (AMC) device discovery, management and control application software

#### **AIRBORNEM2M™ DUAL BAND WIRELESS**

The AirborneM<sub>2</sub>M<sup>™</sup> line of enterprise wireless Ethernet Routers and Bridges are built for networking equipment in an array of machine to machine (M<sub>2</sub>M) applications. The small compact form factor, integrated options and ease of use make it ideal for commercial enterprise environments.

### **Dual-Band Wi-fi**

The AirborneM2M<sup>™</sup> products establish wireless connections over both 2.4 GHz and 5 GHz bands. Whenever the 2.4 GHz airspace is overcrowded with competing wireless transmission, AirborneM2M™ products can be switched over to 5 GHz band to keep data flowing.

#### **Enterprise Class Security**

Security protocols are important to mission-critical wireless M2M applications. AirborneM2M™ multi-layered security approach addresses the requirements of Enterprise-class networks and corporate IT departments. These advanced security features include wireless security (801.11i/WPA2 Enterprise); network security (EAP authentication and certificate support): communication security (SSH functionality and fully encrypted data tunnels); and device security (multi-level encryption capability to protect configuration data).

## SpeedLink™ Roaming

The latest AirborneM2M<sup>™</sup> SpeedLink<sup>™</sup> roaming feature further enhances the high level of connection reliability. SpeedLink™ enables AirborneM2M<sup>™</sup> devices to roam quickly and freely throughout a wireless network without loosing important data. If you're walking around a hospital or driving through a warehouse, SpeedLink™ ensures you stay connected.

#### **ORDERING INFORMATION**

MODEL NUMBER	DESCRIPTION
AirborneM2M™ Ent	erprise Series
ABDN-ER-DP551	Dual Band 802.11a/b/g/n (2.4 GHz, 5 GHz) Ethernet bridge and router with WPA2-Enterprise, WPA, WEP, EAP Security Support Advanced Enterprise Security
ABDN-ER-DP553	Dual Band 802.11a/b/g/n (2.4 GHz, 5 GHz) Ethernet bridge

and router OEM Version (open board, without enclosure)

#### World-wide.

Check with your local distributor for availability and options.

# AIRBORNEM2MTM ENTERPRISE MODELS OPERATE IN A WIDE-RANGE OF COMMERCIAL APPLICATIONS:

**Medical Devices** Retail / Point of Sale Material Handling & Logistics Test & Measurement Security & Access control

# Dual Band (2.4 GHz, 5 GHz) Ethernet Bridge/Router AirborneM2M<sup>TM</sup> Enterprise Series



#### **SPECIFICATIONS**

SPECIFICATIONS		
TECHNOLOGY		
Technology	IEEE 802.11a/b/g/n, Wi-Fi compliant	
Wired Interface	10/100 Ethernet port (Bridge, Router (NAT3) Modes)	
Frequency	2.4 ~ 2.4835 GHz (US/Canada/Europe) 5.150 ~ 5.350 GHz 5.725 ~ 5.825 GHz	
Modulation Technology	DSSS, CCK, OFDM	
Modulation Type	DBPSK, DQPSK, CCK, BPSK, QPSK, 16QAM, 64QAM	
Network Access Modes	Infrastructure (Client), Ad Hoc	
	US/Canada: 11 Channels 802.11b/g 13 Channels 802.11a	
Channels	Europe: 13 Channels 802.11b/g 19 Channels 802.11a	
	France: 4 Channels 802.11b/g	
Wireless Data Rate	802.11b = 11, 5.5, 2, 1 Mbps 802.11a/g = 54, 48, 36, 24, 18, 12, 9, 6 Mbps 802.11n = 65, 58.5, 42, 39, 26, 19.5, 13, 6.5 Mbps	
MAC	CSMA/CA with ACK, RTS, CTS	
Network Protocols	TCP/IP, ARP, ICMP, DHCP, DHS, UDAP, TFTP, UDP, PING	
Receive Sensitivity 802.11 b/g	54Mb/s = -72 dBm 36Mb/s = -78 dBm 18Mb/s = -84 dBm 6Mb/s = -89 dBm 11Mb/s = -86 dBm 1Mb/s = -92 dBm	
Receive Sensitivity 802.11 a	54Mb/s = -74 dBm 36Mb/s = -80 dBm 18Mb/s = -86 dBm 6Mb/s = -90 dBm	
Dimensions	63.4 x 99.0 x 46.7 mm (2.6 x 4.0 x 1.9 in)	

802.11b 15 dBm (31.6mW) 802.11g 12.6dBm (18.12mW) 802.11a 17 dBm (50.1mW)
Disabled, WEP 64 & 128bit, WPA (TKIP), WPA (AES), WPA2 (AES), 802.1x (EAP) Supplicant 802.11I, WPA & WPA2 Enterprise supplicants (EAP-TLS, EAP-TTLS(MSCHAPv2), EAPTTLS (MDS5), EAP-PEAPv0 (MSCHAPv2, LEAP), EAP-FAST, LEAP) Supports Certificates and Private Key Upload and Storage (Multiple)
Integrated RP-SMA Omni-directional 2dBi 2.4/5 GHz Antenna
5.0VDC+/-5%
3000mA (MAX) for 20ms
Operating Current (Tx, 802.11g) = 370mA Typ. Operating Current (Rx, 802.11g) = 200mA Typ.
Operating Temperature: -20° to +85°C Storage Temperature: -20° to +85°C Relative humidity: 5% - 95% (non-condensing) Vibration: 20G peak-to-peak, 20Hz-2KHz swept Shock: 1500G peak-to-peak, 0.5mS duration
10/100 Ethernet
Nylon (Gray)
3 indicator LEDs (Power, LINK, COMM)
North America: FCC Title 47 Part 15 Class B Sub C Intentional Radiator, IOC RSS210 Europe: CE ETSI EN300 328 ROHS & WEEE compliant

#### **MECHANICAL DIAGRAM**

**Model ABDN-ER-DP553** 

Dimensions are in mm



