


2 kV

**Product Description**

CPE jacket
90°C,
2 kV UL
UL Listed

Applications

Portable or fixed power cable for use in drilling rigs, diesel-electric locomotives, railroad and transit car wiring, where reliability is a prime concern. Also suitable for electrically-driven earth-moving equipment, water-heater leads, power and control jumpers, case wiring and motor leads.

Specifications

- CONDUCTOR: Extra flexible, tinned, annealed, stranded copper, suitable separator may be used between conductor and insulation. Conductor sizes per AAR 589
- INSULATION: Ethylene Propylene Rubber (EPR) meeting requirements of ICEA S-95-658 (NEMA WC70)
- OVERALL JACKET: CPE
- STANDARDS: UL Listed RHH/RHW per UL 44 requirements. Meets CSA standards
- AMPACITY: Based on a single conductor in free air per NEC Table 310.17, an ambient temperature of 30°C and a conductor temperature of 90°C
- TEMPERATURE: 90°C
- VOLTAGE: 2 kV UL

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.

Single conductor also available in Type W. Diameters and weights may vary among manufacturers.

Part No.	Conductor Size Circular Mils	Approx. Size AWG/kcmil	No. of Strands	Insulation Thickness (in.)	Overall Jacket Thickness (in.)	Nom. O.D. (in.)	Approx. Wt. lb./1,000 ft.	Amps per Conductor
5N-1401-CPE	4,105	14	19	0.045	0.015	0.210	34	35
5N-1201-CPE	6,088	12	19	0.045	0.015	0.240	45	40
5N-1001-CPE	10,910	10	27	0.045	0.015	0.260	60	55
5N-0801-CPE	14,950	8	37	0.055	0.030	0.326	86	80
5N-0601-CPE	24,640	6	61	0.055	0.030	0.365	124	105
5N-0401-CPE	42,420	4	105	0.055	0.030	0.460	198	140
5N-0201-CPE	60,600	2	147	0.055	0.030	0.498	261	190
5N-0101-CPE	90,900	1	224	0.065	0.045	0.618	400	220
5N-1011-CPE	111,100	1/0	266	0.065	0.045	0.664	468	260
5N-2021-CPE	131,300	2/0	323	0.065	0.045	0.704	561	300
5N-3031-CPE	181,800	3/0	418	0.065	0.045	0.789	725	350
5N-4041-CPE	222,200	4/0	532	0.065	0.045	0.839	888	405
5N-2621-CPE	262,600	262.6	646	0.075	0.065	0.973	1,048	467
5N-3131-CPE	313,100	313.1	777	0.075	0.065	1.029	1,227	522
5N-3731-CPE	373,700	373.7	925	0.075	0.065	1.094	1,436	591
5N-4441-CPE	444,400	444.4	1,110	0.075	0.065	1.169	1,691	652
5N-5351-CPE	535,300	535.3	1,332	0.090	0.065	1.295	2,034	728
5N-6461-CPE	646,400	646.4	1,591	0.090	0.065	1.368	2,395	815
5N-7771-CPE	777,700	777.7	1,924	0.090	0.065	1.488	3,050	904

Electrical and Electronic Wire & Cable • Enterprise Cabling & Security Solutions • Fasteners

Anixter Inc. World Headquarters • 2301 Patriot Boulevard, Glenview, IL 60026-8020 • 1.800.ANIXTER • 224.521.8000 • anixter.com

Anixter is a leading global supplier of communications and security products, electrical and electronic wire and cable, fasteners and other small components. We help our customers specify solutions and make informed purchasing decisions around technology, applications and relevant standards. Throughout the world, we provide innovative supply chain management solutions to reduce our customers' total cost of production and implementation.

Anixter does not manufacture the items described in this publication. Any applicable product warranties are provided by the manufacturers. To the fullest extent permitted by law, Anixter disclaims all warranties, either express or implied.

The information provided and any images shown are for descriptive purposes only. Anixter makes no warranty or representation, express or implied, about the accuracy or completeness of any information provided. Data and suggestions made in the publication are not to be construed as recommendations to purchase or as authorizations to use any products in violation of any law or regulation. All products are sold subject to Anixter's General Conditions of Sale.