

Ethernet-based, Modular Media Converters Chassis

MediaConverter/1



PRODUCT FEATURES

- Supports Ethernet, Fast Ethernet and Gigabit Ethernet
- Supports McPIMs, McLIMs, and McGigabit modules
- Table-top
- 1-slot chassis
- AC power
- Modular, hot-swappable architecture reduces operational costs associated with product installation, upgrades and maintenance

Your network is growing and many new access points, workstations, etc. are required. However, legacy equipment, along with your existing wiring infrastructure, must work with any new equipment you implement in your network. When copper-to-fiber conversions are required, along with advanced troubleshooting features, our MediaConverter/1 is the perfect solution.

The unmanaged B&B Electronics' MediaConverter/1 enables you to easily and cost-effectively connect one type of media to other dissimilar media or networking products. This series increases the functionality and extends the productive life of both your legacy cabling infrastructure and networking equipment when adding fiber to your network.

ORDERING INFORMATION

MODEL NUMBER	DESCRIPTION
MediaConverter/1	
851-10901	1 Slot, AC

ACCESSORIES

895-39949 - Rackmount Shelf

Ethernet-based, Modular Media Converters Chassis

MediaConverter/1



SPECIFICATIONS

TECHNICAL

Single slot AC chassis to house the following modules: McPIM, McLIM, McLIM 10/100 and McGigabit

MECHANICAL

Dimensions 1.64"H x 4.75"W x 5.5"D
(4.16cm H x 12.06cm W x 13.97cm D)

Shipping Weight 2 lbs (.9 kg)

POWER

115/230 or 120-240 VAC, 50/60Hz, 0.3A/0.15A

ENVIRONMENTAL

Operating Temperature: +32° to +122° F (0° to +50° C)
DC Terminal Block

Storage Temperature: 13° to +158° F (-25° to +70° C)

Operating Humidity 5% to 95% (non-condensing),
0 – 10,000 ft. altitude

REGULATORY APPROVALS

FCC Class A, UL/CUL, CE, CSA

MECHANICAL DIAGRAM

(dimensions in inches)

