

# ES GL840ES-2448 SERIES



Shown with optional accessories,  
drawings can be found on page 136

## **DIMENSIONS:**

84"H x 24"W x 48"D

Maximum rail placement: 35"; Usable inside depth: 46"  
13" of dedicated cable management/PDU depth in rear

**RACK SPACES:** 44 RMU • 19" EIA 310-D Compliant

**STOCK COLORS:** Black or Advantage White

## **WEIGHT CAPACITY:**

2000 lbs. on levelers or bolted to floor; 1800 lbs. on casters

## **SHIPPING WEIGHT AND PALLET SIZE:**

475 lbs./90"H x 32"W x 52"D

## **GL840ES-2448MS COMPLETE ENCLOSURE INCLUDES PARTS BELOW**

### **PART NO.**

8401ES-2448

### **DESCRIPTION**

Frame with two pairs of black powder coated, universal 19" M6 mounting rails (with RMU markings) and package of M6 hardware; includes two pairs of PDU mounting brackets with six holes each

7209-N

One Set of 4 Adjustable Levelers (2.5"H)

TPES-S

Solid Top Panel

8402E-MC24

Front Contour Mesh Door with locking handle

8402E-MC24

Rear Contour Mesh Door with locking handle

8410-36ELS

Pair of Solid Lift-off Side Panels with lock and finger release latches

## **ADDITIONAL CONFIGURATIONS**

GL840ES-2448MSS

Complete enclosure with Contour Mesh Front Door and Split Mesh Rear Door

GL840ES-2448MSFS

Complete enclosure with Contour Mesh Front Door and Split Fan Rear Door

GL840ES-2448LC

Localized Containment Kit: Complete enclosure with Contour Mesh Front Door, Solid Rear Door, Air Manager, Air Manager Fan Tray (600 CFM), Exhaust Chimney with an 18" to 32" adjustable range, Chimney Fan Tray (1200 CFM), and Brush Grommet Kit

GL840ES-2448LCHF

Localized Containment Kit: Same as above except with 940 CFM Air Manager Fan Tray and 2260 CFM Chimney Fan Tray