

N NEMA 12 ENCLOSURE



Hinge and Gasketing



Heavy Duty Handle with 3 point latch



Cable Access Knockouts



NEMA 12 Free Standing Enclosures are constructed to be compliant with the National Electrical Manufacturers Association's Type 12 standard. NEMA 12 enclosures, intended for indoor use, protect equipment against dust, falling dirt, water and non-corrosive liquids.

DIMENSIONS: 84"H x 24"W x 42"D
Maximum rail placement and usable inside depth: 38"

RACK SPACES: 45 RMU • 19" EIA 310-D Compliant

STOCK COLOR: Black

WEIGHT CAPACITY: 2000 lbs.

SHIPPING WEIGHT AND PALLET SIZE:
500 lbs./90"H x 38"W x 45"D

PART NO.	DESCRIPTION
GL840N12-2442	NEMA Type 12 Enclosure

ACCESSORIES PART NO.	DESCRIPTION
FFKN12-A1	Fan Assembly (includes filter) and exhaust filter, 230 CFM, 115V
FFKN12-A2	Fan Assembly (includes filter) and exhaust filter, 295 CFM, 115V
FFKN12-A3	Fan Assembly (includes filter) and exhaust filter, 368 CFM, 115V
FILTER-09	Package of five replacement filters for fan kits

Each Ice Qube AC Unit* is UL listed and has a digital temperature controller with alarm, built in condensate evaporator, and contains CFC-free refrigerant. Ice Qube AC Units are warranted by Ice Qube for a period of 1 year from invoice date.

GL2500V	Ice Qube AC Unit, 2500 BTU, 120V, 7.3 amps
GL3500V	Ice Qube AC Unit, 3500 BTU, 120V, 8.2 amps
GL4500V	Ice Qube AC Unit, 4500 BTU, 120V, 9.5 amps
GL6000V	Ice Qube AC Unit, 6000 BTU, 120V, 0.9 amps



Drawings can be found on page 140