



FEATURES

- 19" EIA 310-D Compliant
- Design and features of a 2 post rack in the convenience of a wall mount
- 12 gauge steel mounting brackets are strong and durable
- #12-24 mounting rails

WALL MOUNT RACK

PART NO.	DESCRIPTION
BS2-WMR-24	48"H x 20.52"W x 12.18"D, Usable depth 12", 24 RMU, Wt. cap. 250 lbs., Shipping wt. 20 lbs.



FEATURES

- 19" EIA 310-D Compliant
- Ideal for patch panels and network panels
- Mounting rails tilt down 90°; provides easy access to back of equipment
- Security cover kit available; consists of lift-off front panel and top cover
- #12-24 mounting holes

TILT PANEL MOUNT

PART NO.	DESCRIPTION
BS2-TPM-818	16.31"H x 19.88"W x 18"D, 8 RMU, Wt. cap. 50 lbs., Shipping wt. 22 lbs.
BS2-TPMC-818	Tilt Panel Mount Cover Kit (includes top cover and front panel)