

Serial Device Servers - 8 port

100 series: RS-232 to Ethernet (LAN)

400 series: RS-232/422-485 to Ethernet (LAN)



PRODUCT FEATURES

- Built-in web server for convenient browser-based configuration and support
- Fast serial baud rates up to 921 kbps and auto-negotiating 10/100 Ethernet speed
- Serial tunneling, IP multicast, virtual COM port modes for flexibility and easy integration
- SNMP support for simple network management
- Surge suppression and +5V Out options

Industry-leading, Device Networking Performance

When you need the ultimate in performance, ease of use and reliability, Quatech™ Serial Device Servers provide the highest throughput and lowest latency available. With budget-friendly prices, you won't find a better price-to-performance ratio!

Overcome Serial Limitations By Network Enabling Devices

Serial devices are used in virtually all industries and are proven to be reliable and robust. But there are drawbacks – cable lengths are limited and costly, COM ports are often in short supply, and attached serial devices are not remotely accessible for monitoring and support. A Quatech™ Device Server overcomes all these limitations. Hardware and drivers are invisible to connected serial devices and their software applications, routing data through an IP network to “virtual” COM ports installed on the host PC.

Installation Wizard Makes It Easy To Get Started

An intuitive Installation Wizard gets you up and running quickly, automatically searching local and remote subnets for installed device servers in seconds. Network settings automatically assigned by DHCP networks are displayed for confirmation. Or enter a static IP address – no bother with telnet sessions, MAC address data entry or special cables. Quatech™ device servers may be managed through the Windows® Device Manager interface or a Web browser, so you can count on trouble-free configuration and maintenance long after the initial installation is completed. Models use the same drivers, manuals and installation wizard to simplify deployment and use.

ORDERING INFORMATION

MODEL NUMBER	NUMBER OF PORTS	INTERFACE	CONNECTOR
ESE-100D	8	RS-232	DB9 male
ESE-400D	8	RS-232/422-485 (MEI)	DB9 male

-400 models: Supports RS-232, RS-422/485 on all serial ports.

-Includes: CD with custom datagram utility with command line interface.

ACCESSORIES

PS-SDS - Replacement Wall transformer 120VAC/DC Power Supply, 5VDC @ 3W, 2.1 MM plug (NA Kit)

DS-RACK-BLK - Rack Mount Kit for ESE models-Black

Serial Device Servers 8 port



100 series: RS-232 to Ethernet (LAN)
400 series: RS-232/422-485 to Ethernet (LAN)

SPECIFICATIONS

SERIAL TECHNOLOGY		NETWORK COMMUNICATIONS	
RS-232	DCD, RxD, TxD, DTR, GND, DSR, RTS, CTS, RI	LAN	10/100 Base T
RS-485 2-Wire	Data +, Data -, GND	NETWORK PHYSICAL LAYER STANDARDS	
RS-422/485 4-Wire	AuxIn-, RxD+, TxD+, AuxOut-, GND, RxD-, AuxOut+, AuxIn+, TxD-	Ethernet	IEEE 802.3 auto-negotiating, auto MDI/MDIX
Serial Connector	DB9M or RJ45	PROTOCOLS	
Data Rate	Up to 921.6k bps	Protocols	UDP, TCP/IP, HTTP, DHCP, ARP, ICMP, SNMP (MIB II)
POWER		IP Mode	DHCP, static IP, custom UDP
Source	Power supply included	TCP/UDP	User definable
Input Voltage	5 VDC	UDP	Unicast, Multicast
Connector	Barrel	OTHER	
Power Consumption	4W (typical)	Connection Mode	Normal, Tunneling, Raw TCP, Auto TCP, Raw UDP
MECHANICAL		Client Connection	Supported
LED Indicators	Power, Link, Speed, Data, Status	Diagnostics	Port Status, Ping Test
Switches	Reset button	Firmware Upgrade	Via web interface
Dimensions	25.35 x 13.72 x 4.97 cm (9.98 x 5.40 x 1.96 in)	CONFIGURATION SOFTWARE	
Enclosure	Metal	OS Compatibility	Windows supported up to and including 32-bit/64-bit Win7 (WHQL signed), Linux (four 2.6.27 kernel)
ENVIRONMENTAL		REGULATORY / CERTIFICATIONS / SAFETY	
Operating Temperature	0 to +70°C (-40 to +70°C, storage)	Compliance	FCC, CE, IC
Operating Humidity	10% to 90% non-condensing		
NETWORK			
SDRAM	8 MB		
FLASH Memory	2 MB		

MECHANICAL DIAGRAM

