



eFlow6N16

Overview

eFlow6N16 is a power supply/charger that converts a 120VAC 60Hz input into sixteen (16) fuse protected selectable 12VDC or 24VDC outputs with a total of 6 amps max. The unit includes a Class 2 rated unswitched aux. output. It also offers a suite of features that includes fire alarm disconnect, over voltage protection, and low power disconnect which prevents deep discharge of stand-by batteries.



Specifications

Input:

- 120VAC, 60Hz, 3.5 amp.
- Input fuse: 5A/250V.

Output:

- Sixteen (16) fuse protected outputs.
- 12VDC or 24VDC @ 6.0 amp supply current.
- Outputs are rated at 2.5 amp.
- Auxiliary Power-Limited output rated @ 1 amp (unswitched).
- Over Voltage Protection.

Battery Backup:

- Built-in charger for sealed lead acid or gel type batteries.
- Maximum charge current 1.54 amp.
- Automatic switch over to stand-by battery when AC fails. Transfer to stand-by battery power is instantaneous with no interruption.

Supervision:

- AC fail supervision (form "C" contacts).
- Battery fail & presence supervision (form "C" contacts).
- Low power shutdown. Shuts down DC output terminals if battery voltage drops below 71-73% for 12V units and 70-75% for 24V units (depending on the power supply). Prevents deep battery discharge.

Fire Alarm Disconnect:

- Supervised Fire Alarm disconnect (latching or non-latching) 10K EOL resistor. Operates on a normally open (NO) or normally closed (NC) trigger.

Electrical:

- Operating temperature: 0° C to 49° C ambient.
- BTU/Hr.:
12VDC: 36.85 BTU/Hr.
24VDC: 73.71 BTU/Hr.
- System AC input VA requirement: 420VA.

Visual Indicators:

- Green AC Power LED indicates 120VAC present.
- AC input, DC output and Battery LED indicators.

Additional Features:

- Short circuit and overload protection.
- Unit is complete with power supply, enclosure, battery leads and cam lock.

Mechanical:

- Enclosure Dimensions (H x W x D approx.):
13.5" x 13" x 3.25" (342.9mm x 330.2mm x 82.55mm)
- Accommodates up to two (2) 12VDC/7AH batteries.
- Product weight (approx.): 8.75 lbs. (3.97 kg).
- Shipping weight (approx.): 9.65 lbs. (4.38 kg).

Agency Approvals



- UL 294 UL Listed for Access Control System Units.
- UL 603 UL Listed for Power Supplies for Use with Burglar-Alarms Systems.
- UL 1481 UL Listed for Power Supplies for Fire Protective Signaling Systems.



- ULC-S318-96 - Power Supplies for Burglar Alarm Systems. Also suitable for Access Control.



- CE - European Conformity

Enclosure Dimensions (*H x W x D approximate*):
13.5" x 13" x 3.25" (342.9mm x 330.2mm x 82.55mm)

