



- VL67** 3.7-12mm auto iris varifocal lens, black metal housing
VL67W 3.7-12mm auto iris varifocal lens, white metal housing

Features

- Extreme weather resistant design is perfect for indoor or outdoor use
- 50' IR range (depending on scene selection), with CDS control for great pictures in low light conditions
- Color by day, BW by night - always get the best possible picture
- Mounting bracket included for wall, ceiling or pedestal use
- IP67 compliant
- Removable and adjustable sunshield
- 5 year warranty

Specifications

Image Sensor.....	1/3" Sony Super-HAD™ II
Resolution.....	420 TV lines
Minimum Illumination.....	0 lux with IR on, .092 Lux IR off, F 1.4
Total Pixels.....	537 (H) x 505 (V) approx. 270K pixels
Effective Pixels.....	510 (H) x 492 (V) approx. 250K pixels
Iris.....	Auto
Electronic Shutter Speed.....	1/60 sec. - 1/100,000 sec.
Number of IR LED.....	18
LED IR Wave Length.....	850 nm
Effective IR Range.....	50'
Video S/N Ratio.....	More than 48dB
Gamma.....	0.45 typ.
Video Signal Output.....	1.0V p-p, 75 Ohms
Scanning System.....	2:1 interlace, EIA standard 525 line 60 fields / second
Synchronization.....	Internal
Backlight Compensation.....	Yes
AGC.....	Yes
CDS Sensor.....	Yes
Operating Temperature/ Humidity.....	14° F - 140° F / 30% - 80% RH
Storage Temperature.....	-4° F - 176° F
Power Consumption.....	12VDC 500mA / 24VAC 6 watts
Power Supply.....	12VDC (power supply not included)
Housing.....	Metal
Weight.....	1.32 lbs.
Included in Package.....	Mounting bracket



Optional Accessory



PSW5
Power Supply

Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 2/2/12

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com