


CVC5835DNV	2.8 - 12mm auto iris varifocal lens, grey housing
CVC5835DNVW	2.8 - 12mm auto iris varifocal lens, white housing
CVC5935DNV	9 - 22mm auto iris varifocal lens, grey housing
CVC5935DNVW	9 - 22mm auto iris varifocal lens, white housing

Features

- 1/3" Sony Super-HAD II™ CCD
- 3DNR (sense-up) - sharp image under ultra low light level
- Intense-IR Function - no saturation image, vivid image
- Defect Function - elimination of white spots
- HSBLC (High Light Suppression BLC)
- Privacy zone
- ICR - removable IR cut filter
- Convenient On-Screen Display (OSD) function controls
- 12VDC / 24VAC dual voltage operation
- IP66 compliant
- 5 year warranty

Specifications

Image Sensor	1/3" Sony Super-HAD II™ CCD
Resolution.....	600 TV lines
Minimum Illumination.....	0.000006 lux (IR LEDs on)
Effective Pixels	768 (H) x 494 (V)
Total Pixels	811 (H) x 508 (V)
Number of IR LEDs	33
IR Range	Up To 65' (depending on scene reflection)
White Balance	ATW / AWB / Manual / AWC - Set
AGC.....	High / Middle / Low / Off
S/N Ratio	52dB (AGC off, weight on)
Backlight Compensation.....	BLC / HSBLC / Off
Electronic Shutter Speed.....	Auto (1/50, 1/60 sec. - 1/100,000 sec.)
OSD.....	Built-In
3DNR.....	On / Off (0 - 100 levels adjustable)
D-WDR	Indoor / Outdoor / Off
Sharpness	0-31' (level adjustable)
Privacy.....	On / Off (8 zones)
Scanning System.....	2:1 interlace
Synchronization	Internal / Line - Lock
Motion Detection.....	On / Off (4 zones)
Sense-Up.....	Off / Auto (selectable limit x2 - x256)
Mirror.....	Off / Mirror / V-Rev / Rotate



Freeze	On / Off
Day/Night.....	Color / BW / Auto / EXT
Digital Zoom	On (32x) / Off
Defect Compensation	Auto: 128 points / Manual: 4 points
Power Supply	12VDC / 24VAC (dual voltage) (power supply not included)
Power Consumption	12VDC, 250mA (CDS off) 12VDC, 700mA (CDS on) 24VAC, 100mA (CDS off) 24VAC, 250mA (CDS on)
Operating Temperature/	
Humidity.....	-4° F – 140° F / RH 95% max.
Storage Temperature/	
Humidity.....	-4° F – 140° F / RH 95% max.
Dimensions.....	5.5" (W) x 4" (H)
Weight	1.2 lbs.

Optional Accessories



PSW4
24VAC
Power
Supply



PSW5
12VDC
Power
Supply



INTWM
Wall
Mount



INTPM
Pendant
Mount



JB02DG grey
JB02DW white
Dome
Junction Box

Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 7/23/13

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880

www.specotech.com