DATASHEET

AXIS T92E Housing Series

Smart features for wide ranging of environments.

AXIS T92E Housing Series protects the Axis network camera in adverse indoor and outdoor

AXIS T92E Housing Series protects the Axis network camera in adverse indoor and outdoor conditions.

AXIS T92E Housing Series is available in two models: AXIS T92E05 Protective Housing and AXIS T92E20 Outdoor Housing.

AXIS T92E20 features an internal shell for storing heat in cold environments. Fan ventilation for hot environments transfers excess to the outer chassis for efficient cooling.

AXIS T92E05/T92E20 feature IP66 and NEMA 4X protection rating against the ingress of dust, windblown dust, rain, high pressure water jets from any direction, hose-directed water, and damage from external ice formation. In addition, they are IK10rated for protection against impact and vandal acts. Easy and quick installation using either Power over Ethernet or High Power over Ethernet connection. The network cable is further protected in the wall mount to enhance the vandal protection.

The Arctic Temperature Control functionality ensures that the cameras can start up even at -40 $^\circ C$ (-40 $^\circ F) following a power failure.$

Various brackets and accessories are available for AXIS T92E Housing Series, such as ceiling and wall brackets, column mounts and adapters. AXIS T92E Series comes with a wall bracket with an internal cable channel and ball joint.




- > IP66- and NEMA 4X-rated
- > IK10-rated
- > One cable installation
- > Arctic Temperature Control







Dimensions: T92E Housing Series and wall mount bracket with internal cable channel



Technical specifications – AXIS T92E Housing Series

AXIS T92E05 Protective Housing				
Supported cameras	Indoor: AXIS M1103, AXIS M1104 Indoor/outdoor: AXIS M1113, AXIS M1114, AXIS P13 Series, AXIS Q16 Series, AXIS Q1755			
Casing	Aluminium casing, polycarbonate sunshield and cable cover. IP66- and NEMA 4X-rated, IK10 impact-resistant aluminum enclosure			
Power	Not required			
Environment	Indoor/outdoor			
Operating conditions	See table below			
Protection rating	IEC 60529 IP66, NEMA 250 Type 4X, IEC 62262 IK10			
Approvals	IEC 60068-2-6, IEC 60068-2-27			
Weight	2.4 kg (5.1 lb)			
Included accessories	VT wall bracket, sunshield, User's Guide, screw driver torx 20			
Warranty	Axis 3-year warranty, www.axis.com/warranty			

AXIS T92E20 Out	door Housing		
Supported cameras	AXIS M1113, AXIS M1114, AXIS P13 Series, AXIS Q16 Series, AXIS Q1755		
Casing	Aluminium casing, polycarbonate sunshield and cable cover. IP66- and NEMA 4X-rated, IK10 impact-resistant aluminum enclosure		
Power	Power over Ethernet (PoE) IEEE 802.3af or High Power over Ethernet (High PoE) Power supply not included		
Environment	Indoor/outdoor		
Operating conditions	See table below Arctic Temperature Control enables camera start-up at temperatures as low as -40 °C (-40 °F)		
Protection rating	IEC 60529 IP66, NEMA 250 Type 4X, IEC 62262 IK10		
Approvals	EN 55022 Class B, EN 61000-3-2, EN 61000-3-3, EN 55024, EN 61000-6-1, EN 61000-6-2, EN 60950-22, IEC 60068-2-6, IEC 60068-2-27, FCC Part 15, Subpart B, Class B, VCCI, Class B ITE, C-tick AS/NZS CISPR 22, ICES-003, Class B		
Weight	2.5 kg (5.5 lb)		
Included accessories	VT wall bracket, sunshield, 2x short Ethernet cables, User's Guide, screw driver torx 20		
Warranty	Axis 3-year warranty, www.axis.com/warranty		

www.axis.com

	otective Housing – Operating conditions		rotective Housing – Operating conditions	
AXIS Q1755	0 °C to 45 °C (32 °F to 113 °F) Humidity 15 - 100% RH (condensing)	AXIS Q1755	PoE IEEE 802.3af: -30 °C to 45 °C (-22 °F to 113 °F) High PoE IEEE 802.3at: -40 °C to 45 °C (-40 °F to 113 °F)	
AXIS Q1602	0 °C to 50 °C (32 °F to 122 °F) Humidity 15 – 100% RH (condensing)	AXIS Q1602	Humidity 15 - 100% RH (condensing) PoE IEEE 802.3af: -30 °C to 50 °C (-22 °F to 122 °F)	
XIS Q1604	0 °C to 50 °C (32 °F to 122 °F) Humidity 15 – 100% RH (condensing)		High PoE IEEE 802.3at: -40 °C to 50 °C (-40 °F to 122 °F) Humidity 15 - 100% RH (condensing)	
AXIS P1353	0 °C to 50 °C (32 °F to 122 °F) Humidity 15 - 100% RH (condensing)	AXIS Q1604	PoE IEEE 802.3af: -30 °C to 50 °C (-22 °F to 122 °F) High PoE IEEE 802.3at: -40 °C to 50 °C (-40 °F to 122 °F) Humidity 15 - 100% RH (condensing)	
AXIS P1354	0 °C to 50 °C (32 °F to 122 °F) Humidity 15 - 100% RH (condensing)	AXIS P1353	PoE IEEE 802.3af: -30 °C to 50 °C (-22 °F to 122 °F)	
AXIS P1355	0 °C to 50 °C (32 °F to 122 °F) Humidity 15 – 100% RH (condensing)		High PoE IEEE 802.3at: -40 °C to 50 °C (-40 °F to 122 °F) Humidity 15 - 100% RH (condensing)	
AXIS P1357	0 °C to 50 °C (32 °F to 122 °F) Humidity 15 - 100% RH (condensing)	AXIS P1354	PoE IEEE 802.3af: -30 °C to 50 °C (-22 °F to 122 °F) High PoE IEEE 802.3at: -40 °C to 50 °C (-40 °F to 122 °F) Humidity 15 - 100% RH (condensing)	
AXIS M1113	–20 °C to 50 °C (-4 °F to 122 °F) Humidity 15 – 100% RH (condensing)	AXIS P1355	PoE IEEE 802.3af: -30 °C to 50 °C (-22 °F to 122 °F) High PoE IEEE 802.3af: -40 °C to 50 °C (-40 °F to 122 °F)	
AXIS M1114	–20 °C to 50 °C (–4 °F to 122 °F) Humidity 15 – 100% RH (condensing)		Humidity 15 - 100% RH (condensing)	
AXIS M1103 Indoor	-20 °C to 50 °C (-4 °F to 122 °F) Humidity 15 - 100% RH (condensing)	AXIS P1357	PoE IEEE 802.3af: -30 °C to 50 °C (-22 °F to 122 °F) High PoE IEEE 802.3at: -40 °C to 50 °C (-40 °F to 122 °F) Humidity 15 - 100% RH (condensing)	
AXIS M1104 Indoor	-20 °C to 50 °C (-4 °F to 122 °F) Humidity 15 - 100% RH (condensing)	AXIS M1113	PoE IEEE 802.3af: -30 °C to 50 °C (-22 °F to 122 °F) High PoE IEEE 802.3at: -35 °C to 50 °C (-31 °F to 122 °F) Humidity 15 - 100% RH (condensing)	
		AXIS M1114	PoE IEEE 802.3af: -30 °C to 50 °C (-22 °F to 122 °F) High PoE IEEE 802.3at: -35 °C to 50 °C (-31 °F to 122 °F) Humidity 15 - 100% RH (condensing)	

More information and a configuration tool is available at www.axis.com/accessories



©2013 Axis Communications AB. AXIS COMMUNICATIONS, AXIS, ETRAX, ARTPEC and VAPIX are registered trademarks or trademark applications of Axis AB in various jurisdictions. All other company names and products are trademarks or registered trademarks of their respective companies. We reserve the right to introduce modifications without notice.