

CVC5300DPVF

2.8 - 12mm DC auto iris varifocal lens, dark grey housing

CVC5300DPVFW

2.8 - 12mm DC auto iris varifocal lens, white housing

Features

- 1/3" Sony Super-HAD II™ CCD
- 600 lines of resolution
- 0.15 lux, 0.00002 lux (IR LEDs on)
- Digital Deterrent™
- PIR activated white LEDs
- IR range up to 65'
- Digital image stabilization
- Full OSD operation
- 3-axis wall or ceiling mount
- Weather resistant operation
- IP66 compliant
- 12VDC / 24VAC dual voltage operation
- 5 year warranty



Specifications

Image Sensor	1/3" Sony Super-HAD II™ CCD
Resolution	600 TV lines
Minimum Illumination	CDS Off: 0.15 lux CDS On: 0.00002 lux
Effective Pixels	811 (H) x 508 (V) 768 (H) x 494 (V)
Number of LEDs	24 IR + 6 white LEDs
IR Range	Up To 65'
White Balance	ATW / Outdoor / Indoor / Manual AWC (1,700°K - 11,000°K)
AGC	High / Low / Off
Backlight Compensation	BLC / HLC / Off
S/N Ratio	More than 52dB
Video Output	CVBS: 1.0Vp-p / 75 Ohm
Electronic Shutter Speed	1/60 sec - 1/120,000 sec
Sharpness	On / Off (level adjustable)
Privacy Masking	On / Off (12 programmable zones)
Scanning Frequency	15.734kHz (H) & 59.94Hz (V)
Scanning System	2:1 interlace
Synchronization	Internal
TV System	NTSC, PAL

Day/Night	Color / BW / Auto
Sense-Up	Auto / Off (selectable x2 - x512)
Motion Detection	On / Off (8 programmable zones)
Digital Zoom	On / Off (1x - 16x)
DIS	On / Off
Flip / Mirror	On / Off
SSDR	On / Off (level adjustable)
SSNR Ill.	On / Off (level adjustable)
Power Supply	12VDC / 24VAC dual voltage operation (power supply not included)
Power Consumption	12VDC, 250mA (CDS off, PIR off) 600mA (CDS on, PIR on) Heater On Adj: 200-600mA 24VAC, 100mA (CDS off, PIR off), 250mA (CDS on, PIR on) Heater On Adj: 120-250mA
Operating Temperature/	
Humidity	-4° F – 140° F / RH 95% max.
Dimensions	4.36" (H) x 5.47" (Dia.)
Weight	3.08 lbs.

Optional Accessories



INTPM
Pendant
Mount



INTWM
Wall Mount



JB03TG
Large Round
Junction Box



PSW4
24VAC
Power Supply



PSW5
12VDC
Power Supply

Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.



Rev. 6/19/12

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com