




CVC5100BPVF 2.8 - 12mm auto iris varifocal lens, grey housing
CVC5100BPVFW 2.8 - 12mm auto iris varifocal lens, white housing

Features

- 1/3" Sony Super-HAD II™ CCD
- 600 TV lines resolution
- True Day/Night capability
- Digital Deterrent™: white LEDs are turned on when motion is triggered
- 24 IR LEDs & 6 white LEDs
- Digital image stabilization
- 12VDC / 24VAC dual voltage operation
- 5 year warranty

Specifications

Image Sensor 1/3" Sony Super-HAD II™ CCD
Resolution..... 600 TV lines
Minimum Illumination..... CDS off: 0.15 lux
CDS on: 0.00002 lux
Effective Pixels 811 (H) x 508 (V)
768 (H) x 494 (V)
Number of LEDs IR: 24, white: 6
IR LED Wavelength 850nm
IR Range Up To 65'
White Balance ATW / Outdoor / Indoor / Manual
AWC (1,700°K - 11,000°K)
AGC..... High / Low / Off
Backlight Compensation BLC / HLC / Off
S/N Ratio More than 52dB
Video Output..... CVBS: 1.0Vp-p / 75 Ohm
Electronic Shutter Speed..... 1/60 sec. - 1/120,000 sec.
Sharpness On / Off (level adjustable)
Privacy Masking On / Off (12 programmable zones)
Scanning Frequency..... 15.734kHz (H) & 59.94Hz (V)
Scanning System..... 2:1 interlace
Synchronization Internal
TV System NTSC
Day/Night..... Color / BW / Auto
Sense-Up..... Auto / Off (selectable x2 - x512)



Motion Detection..... On / Off (8 programmable zones)
Digital Zoom On / Off (1x - 16x)
DIS..... On / Off
Flip/Mirror On / Off
SSDR..... On / Off (level adjustable)
3DNR..... On / Off (level adjustable)
Power Supply 12VDC / 24VAC
dual voltage operation
(power supply not included)
Power Consumption 12VDC, 250mA (CDS off, PIR off)
600mA (CDS on, PIR on)
Heater on adj: 200 - 600mA
24VAC 100mA (CDS off, PIR off),
250mA (CDS on, PIR on)
Heater on adj: 120 - 250mA
Operating Temperature/
Humidity..... - 4° F – 140° F / RH 95% Max.
Storage Temperature/
Humidity..... - 4° F – 140° F / RH 95% Max.
Dimensions..... 3.7" (W) x 3.93" (H) x 11.22" (L)
Weight 3.5 lbs.

Optional Accessories



CVCJBB
Bullet Camera
Junction Box



INTJBS
Square
Junction Box



INTCM
Corner/Pole
Adaptor



PSW4
24VAC
Power Supply



PSW5
12VDC
Power Supply

Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 2/25/13

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com