


“HORNET” + PVC



ANIXTER PART NO. HORNET-PVC

CONSTRUCTION

		<u>Nom. Diameter</u>
CONDUCTOR :	150sqmm (19/3.25mm) aluminium to BS215 Part 1 “UNGREASED”	16.25mm
LAY LENGTH:	1st Layer, 97.5mm minimum, 136.5mm maximum 2nd Layer, 162.5mm minimum, 227.5mm maximum	
INSULATION :	BLACK PVC	19.5mm

MECHANICAL CHARACTERISTICS

APPROX. WEIGHT:	694 kg/km
RTS:	24.7 kN
MODULUS OF ELASTICITY:	55900 N/mm ²
COEFFICIENT OF LINEAR EXPANSION:	23 x 10 ⁻⁶ per °C

ELECTRICAL CHARACTERISTICS

MAX. DC CONDUCTOR RESISTANCE @ 20°C:	0.1825 ohms/km
--------------------------------------	----------------



Drawing No:	Issue 1	Date:	03/06/2009
Manf Ref:	HORNET-PVC	Page No:	1