

Universal Flameproof & Increased Safety Gland with Inner & Outer Seals

- Suitable for wire braid, single wire, steel tape and strip armoured plastic or rubber sheathed, extruded bedded cables.
- Outer seal grips sheath of cable.
- Inner seal grips bedded layer of cable.
- Weatherproof and waterproof.
- Inner and outer seal rated to IP66.
- Design has separate outer locking ring.
- Gland rated to IP66 with use of suitable sealing washer or thread sealant at gland interface.
- For use with flameproof equipment or increased safety equipment (E.Exd or E.Exe).
- Complies with group IIA, IIB, IIC hazardous atmospheres (EN 60079).
- ATEX Certified.
- Zone 1 and Zone 2 applications.
- Incorporates external boot seal which offers protection against moisture ingress to the armour.

Anixter Number	Gland Manu	Gland Size	Cable Dimensions Accommodated (mm)			
			Under Armour		Overall	
			Minimum	Maximum	Minimum	Maximum
E1DZ-UNI-20SS	HAWKE	20SS	3.0	8.1	5.5	12.0
E1DZ-UNI-20S	HAWKE	20S	6.5	11.9	9.5	16.0
E1DZ-UNI-20	HAWKE	20	8.4	14.3	12.5	20.5
E1DZ-UNI-25	HAWKE	25	11.1	20.2	16.9	26.0
E1DZ-UNI-32	HAWKE	32	17.6	26.5	22.0	33.0
E1DZ-UNI-40	HAWKE	40	23.1	32.5	28.0	41.0
E1DZ-UNI-50	HAWKE	50	28.9	44.4	36.0	52.6
E1DZ-UNI-63	HAWKE	63	39.9	56.3	46.0	65.3
E1DZ-UNI-75	HAWKE	75	50.5	68.2	57.0	78.0