


ANIXTER LTD



This drawing and information is copyright to Anixter Ltd therefore information may not be used without written permission from Anixter Ltd

DESIGN -	NOM DIA. mm
Conductor: 24AWG PAC	0.50
Insulation: Polyolefin	0.90
Pairing:	1.80
Layup:	4.36
Sheathing: HDPE Black	4.75

ELECTRICAL CHARACTERISTICS @ 20 °C

Characteristic Impedance (1-10&20-100MHz)	100 +/- 15
Characteristic Impedance (10-20MHz)	100 +/- 12
DC Conductor Loop Resistance	19 /100m
Max. Resistance Unbalance	2%
Nominal Velocity of Propagation	66%
Nominal Capacitance	50 pF/m
Max. Capacitance Unbalance	1600 pF/m
Insulation Resistance (500V)	2000 MegOhms/km

CABLE PROPERTIES

Minimum Installation Bend Radius	8 x Dia.
Minimum Installed Bend Radius	4 x Dia.
Installation Temperature Range - Installed	0 to 50 °C
Operating Temperature Range	-20 to 60 °C
Approximate Weight (kg)	30
Standard Reel Lengths (m)	1000

CAT 5e UTP cable, External Grade - Anixter Part No. CM-00424UTP-5E-DUCT

DRAWING No: LCD 071008A

ISSUE No: 3

SCALE: not to scale

DATE: 08/10/07