# UML Family 46-inch High Performance HD LED monitor

www.boschsecurity.com

















- ► Full HD 1920 x 1080 resolution
- ▶ Precise color reproduction
- ► HDMI, DVI, VGA, S-Video inputs
- ▶ Super-slim bezel for seamless tiled wall mounting
- ▶ High contrast ratio of 3500:1

The Bosch UML-463-90 High Performance LED monitor is a 1080p Full HD resolution color monitor ideal for use with digital video recorders (DVRs), and with PC applications. The monitor features a color LCD flatscreen panel with a 46-inch viewable picture area. The monitor features a wide range of horizontal and vertical viewing angles that provide comfortable, clear viewing – whether you mount it to a wall, ceiling or on a desktop.

#### Functions

#### **Excellent image quality**

The Bosch High Performance HD LED monitors automatically adapt to the input resolution of the incoming video signal, and support up to 1920 x 1080 resolution (Full HD). The monitors' analog VGA input easily accommodates the widespread use of PCs in today's security surveillance systems. Their high contrast ratio (3500:1) and a high brightness setting offers excellent color accuracy and imaging for easier viewing and interpretation of images. The panel can refresh in as little as 6.5 milliseconds, so you get crisp, clear images with less smearing - and less image "ghosting" in fast-motion video.

#### **Tiled wall mounting**

The super-thin bezel screen surround means the wall mounted monitors can be precisely arranged in a tiled configuration. Especially suited for control room environment with multiple camera connections.

#### **Certifications and approvals**

| Region | Safety Certification                             |
|--------|--|
| Canada | cUL  |
| Europe | EN60950, CE Declaration of Conformity, CB scheme |
| USA    | UL60950  |

#### Electromagnetic Compatibility (EMC)


| Emission | EN55022:2010 class B, FCC part 15 class B |
|----------|---|
| Immunity | EN55024:2010, EN50130-4:2011              |

#### Environmental


Vibration Energy Star 6.0

| Region | Certification |
|--------|---------------|
| Europe | CE            |


### Installation/configuration notes



UML-463-90: Front View



UML-463-90: Side View



UML-463-90: Back View

### Parts included

| Quant. | Component  |
|--------|--|
| 1      | Bosch Full HD Color LED Flat Panel Monitor   |
| 2      | Power Cords, 3-wire with grounded plug 1.8 m (6 ft) long: one with a U.S plug type and one with a European Continental plug type |
| 1      | 1 DVI-D to DVI-D cable, 1.8 m (6 ft)   |
| 1      | 1 VGA to VGA (D-Sub), cable, 1.8 m (6 ft)  |
|        |  |

- 1 Remote control
- 2 AAA batteries for remote control
- 1 Installation Manual (English)
- 1 CD-ROM with multi-language Installation Manual

#### **Technical specifications**

#### **Electrical**

| Rated Voltage          | 120/230 VAC, 50/60 Hz                       |
|------------------------|---|
| Voltage Range          | 100-240 VAC, 50/60 Hz                       |
| Frequency              | Horizontal: 60–73 KHz<br>Vertical: 47–63 Hz |
| Power at Rated Voltage | On = 149 W<br>Active Off = 0.5 W            |

#### Video

| Sync Format   | PAL/NTSC automatic detection                    |
|---|---|
| LCD Panel   | LED backlight                                   |
| Viewable Picture Area   | 46 in.  |
| Active Display Area<br>(H x V)  | 1018.08 x 572.67 mm<br>(40.08 x 22.55 in.)      |
| Pixel Pitch<br>(H x V):   | 0.53025 x 0.53025 mm<br>(0.02088 x 0.02088 in.) |
| Resolution <sup>1</sup>   | 1920 x 1080                                     |
| Aspect Ratio  | 16:9  |
| Display Colors  | 1073.7 million                                  |
| Response Time   | 6.5 ms (typical)                                |
| Backlight   | 50,000 hours                                    |
| 1. Pixel Policy: Bosch monitors follow the ISO 13406-2 Class II standard. |   |

## LCD Panel Optical Characteristics

| Luminance      | 450 cd/m² (typical)                 |
|----------------|-------------------------------------|
| Contrast Ratio | 3500:1 (typical)                    |
| Viewing Angle  | Horizontal/Vertical: 178° (typical) |

#### Video Input

| Composite<br>Video (CVBS) | 1.0 Vp-p (0.5–1.5 Vp-p), automatic switching from 75 Ohm unbalanced termination to Hi-Z with passive loop-through operation |
|---------------------------|---|
| Y/C (S-video)             | 0.7 Vp-p (Y-signal), 0.3 Vp-p (C-signal), 75 Ohm termination  |
| Component                 | Y, Pb, Pr   |
| Digital Inputs            | DVI D (1 x) and HDMI (2 x)  |
| VGA (RGB<br>PC)           | 0.7 Vp-p (0.5–1 Vrms)   |
| Audio Input               | 2.0 V line level, mono  |

| RGB and DVI             | HDMI                      |
|-------------------------|---------------------------|
| 640 x 480 (60/72/75 Hz) | 640 x 480 (60/72/75 Hz)   |
| 720 x 400 (70 Hz)       | 720 x 400 (70 Hz)         |
| 800 x 600 (60/75 Hz)    | 800 x 600 (60/75 Hz)      |
| 1024 x 768 (60/75 Hz)   | 1024 x 768 (60/75 Hz)     |
| 1280 x 768 (60 Hz)      | 1280 x 768 (60 Hz)        |
| 1280 x 960 (60 Hz)      | 1280 x 960 (60 Hz)        |
| 1280 x 1024 (60 Hz)     | 1280 x 1024 (60 Hz)       |
| 1360 x 768 (60 Hz)      | 1360 x 768 (60 Hz)        |
| 1366 x 768 (60 Hz)      | 1366 x 768 (60 Hz)        |
| 1400 x 1050 (60 Hz)     | 1400 x 1050 (60 Hz)       |
| 1600 x 1200 (60 Hz)     | 1600 x 1200 (60 Hz)       |
| 1680 x 1050 (60 Hz)     | 1680 x 1050 (60 Hz)       |
| 1920 x 1080 (60 Hz)     | 1920 x 1080 (60 Hz)       |
|                         | 480i (60 Hz)              |
|                         | 480p (60 Hz)              |
|                         | 576i (50 Hz)              |
|                         | 576p (50 Hz)              |
|                         | 720p (25/3050/60 Hz)      |
|                         | 1080i (50/60 Hz)          |
|                         | 1080p (24/25/30/50/60 Hz) |
|                         | 1080p (24/25 Psf)         |

#### Controls

| nput |
|------|
|      |

| Rear Control Panel       | Push-buttons   |
|--------------------------|--|
| Rear Control Panel       | Push-bullons   |
| Remote control           | Push-buttons   |
| Video Source             | Selects: Component Video, S-video, VGA, HDMI, DVI-D  |
| Menu                     | Selects on-screen display (OSD), up cursor, down cursor/auto adjust, left cursor, right cursor |
| Power                    | On/Off   |
| Control Panel<br>Lockout | Multiple push-button combination   |
|                          |  |

#### On-screen Display

### Indicators (on rear)

| LED | Power On (green)         |
|-----|--------------------------|
|     | Power Off, Standby (red) |

| Connectors    |   |
|---------------|---|
| Video 1 (AV1) | Composite video: two (2) BNC (1 in, 1 out)  |
| Digital       | Two (2) (1 DVI-D in, 1 DVI-D out)   |
| IR            | Two (2) (1 in, 1 out)   |
| Display port  | One (1) in  |
| HDMI          | Two (2) in  |
| VGA           | One (1): 1 RGB 15-pin D-sub in, 1 RGB 15-pin D-sub out  |
| Component     | One (1): Y, Pb, Pr  |
| Y/C (S-video) | One (1) mini-DIN, 4-pin (1 in)  |
| Audio         | 1 Audio In: RCA (right/left)<br>1 Audio In: phono jack<br>1 Audio Out: RCA (right/left)<br>1 Speaker Out (right/left) |
| RS-232        | Two (2) (1 in for firmware update, 1 out for firmware update)   |
| Power Input   | 100 - 240 VAC   |
| Power Output  | 100 – 240 VAC   |

#### Mechanical

| Cabinet Material            | SECC   |
|-----------------------------|--|
| Finish                      | Black  |
| Mount                       | Wall mounting compatible with standard bracket (optional)<br>Desk mount (optional) |
| VESA Mounting<br>Compliance | 400 x 400 mm (15.7 x 15.7 in.)   |

#### Dimensions (WxHxD)

| Monitor        | 1023.68 x 578.27 x 111.8 mm<br>(40.30 x 22.77 x 4.4 in.) |
|----------------|--|
| With Packaging | 1190 x 754 x 290 mm<br>(46.85 x 30.08 x 11.42 in.)       |

#### Weight

| Monitor Weight  | 25 kg (55.12 lb) |
|-----------------|------------------|
| Shipping Weight | 30 kg (66.14 lb) |

#### **Environmental**

| Operating<br>Temperature | 0°C to +50°C (32°F to 122°F) |
|--------------------------|------------------------------|
| Storage<br>Temperature   | 0°C to +50°C (32°F to 122°F) |
| Humidity                 | 0% to 90% Relative           |

### **Ordering information**

UML-463-90 46-inch High Performance HD LED Monitor Order number UML-463-90

#### 4 | UML Family 46-inch High Performance HD LED monitor

#### **Accessories**

#### **UMM-LED46-SD Desktop Stand**

Order number UMM-LED46-SD

#### Represented by:

#### Americas:

Americas:
Bosch Security Systems, Inc.
130 Perinton Parkway
Fairport, New York, 14450, USA
Phone: +1 800 289 0096
Fax: +1 585 223 9180 security.sales@us.bosch.com www.boschsecurity.us

#### Europe, Middle East, Africa:

Bosch Security Systems B.V. P.O. Box 80002 5617 BA Eindhoven, The Netherlands Phone: + 31 40 2577 284 Fax: +31 40 2577 330 emea.securitysystems@bosch.com www.boschsecurity.com

#### Asia-Pacific:

Robert Bosch (SEA) Pte Ltd, Security Systems 11 Bishan Street 21 11 Bishan Street 21 Singapore 573943 Phone: +65 6571 2808 Fax: +65 6571 2699 apr.securitysystems@bosch.com www.boschsecurity.asia

China:
Bosch (Shanghai) Security Systems Ltd.
201 Building, No. 333 Fuquan Road
North IBP
Changning District, Shanghai
200335 China
Phone +86 21 22181111
Fax: +86 21 22182398 www.boschsecurity.com.cn

#### America Latina:

America Latina:
Robert Bosch Ltda Security Systems Division
Via Anhanguera, Km 98
CEP 13065-900
Campinas, Sao Paulo, Brazil
Phone: +55 19 2103 2860
Fax: +55 19 2103 2862
latam.boschsecurity@bosch.com
www.boschsecurity.com