

2-channel analog output module; 0-10 V; 10 bits; 10 mA

Item No.: 750-560



2-channel analog output module; 0-10 V; 10 bits; 10 mA

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	750-560
EAN	4045454501327
Content	1
Order amount	1
Customer item number	

Notes

The analog output module generates signals of a standard magnitude 0–10V. The output signal is electrically isolated and transmitted with a resolution of 10 bits. The outputs are short-circuit proof. Each channel is equipped with an LED to indicate short-circuits or overloads 15mA. The shield (screen) is directly connected to the DIN rail. Both the internal system and field side supply are used to power the module. The output channels have one common ground potential. The analog outputs and the 24V supply have one common ground potential so that actuators such as servo drives can be connected using a 3-conductor cable.

Technical data

Miscellaneous

Color	light gray
Conformity marking	CE
No. of outputs	2
Isolation	500 V system/supply
Voltage via power jumper contacts	24 V AC/DC

Technical data	
Current consumption (internal) [mA]	16 [mA]
Signal voltage	0 V ... 10 V
Load impedance	1 k
Conversion time	approx. 10 ms
Measuring error (25°C)	< ± 0.2 % of the full scale value
Temperature coefficient	< ± 0.02 % /K of the full scale value
Resolution [bits]	10 [bits]
Bit width	2 x 16 bits data 2 x 8 bits control/status (option)
Degree of protection	IP20
Connection technology (1)	CAGE CLAMP®
Cross section from (1) [mm²]	0.08 [mm²]
Cross section up to (1) [mm²]	2.5 [mm²]
Cross section from (1) [AWG]	28 [AWG]
Cross section up to (1) [AWG]	14 [AWG]
Stripped length from (1) [mm]	8 [mm]
Stripped length up to (1) [mm]	9 [mm]
Stripped length (1) [in]	0.33 [in]
Fire load [MJ]	1.288 [MJ]
Weight [g]	53.5 [g]
Width [mm]	12 [mm]
Width [in]	0.472 [in]
Height [mm]	64 [mm]
Height [in]	2.52 [in]
Length [mm]	100 [mm]
Length [in]	3.937 [in]
Storage temperature	-25 °C ... +85 °C
Relative air humidity (no condensation) [%]	95 [%]
Type of mounting	DIN 35 rail
Operating temperature	0°C ... +55°C
EMC: CE - emission of interference	acc. to EN 61000-6-4 (2007)
EMC: CE - immunity to interference	acc. to EN 61000-6-2 (2005)
Shock resistance	acc. to IEC 60068-2-27
Vibration resistance	acc. to IEC 60068-2-6

Approbation

Item No.	Registration	Registration no.	Voltage [V]	Current [A]	Cross section [mm², AWG]
750-560	BSH	Bescheinigung Nr. 467			
750-560	IECEX	IECEX TUN 09.0001 X			
750-560	TUEV	TUEV 07 ATEX 554086 X			
750-560	UL	E198726 Sec.1			
750-560	UL	E175199 Sec.1			

Accessories

Carrier rail

Item no.	Description	Pack. unit (Sub Pack)
210-112	Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to en 60715; "Hole width 25 mm	1
210-113	Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; according to en 60715	1
210-114	Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; according to en 60715	1
210-115	Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to en 60715; "Hole width 18 mm	1
210-118	Steel carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to en 60715	1
210-196	Aluminum carrier rail; 35 x 8.2 mm; 1.6 mm thick; 2 m long; unslotted; according to en 60715	1
210-197	Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; according to en 60715	1
210-198	Copper carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to en 60715	1
210-504	Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; galvanized; according to EN 60715	1
210-505	Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; galvanized; according to EN 60715	1
210-506	Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; galvanized; ähnlich EN 60715	1
210-508	Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; galvanized; ähnlich EN 60715	1

Accessories*Marking accessories*

Item no.	Description	Pack. unit (Sub Pack)
2009-145	Mini-WSB Inline; plain; 1,700 Mini-WSB markers (5 mm) on roll; stretchable 5 - 5.2 mm	1
248-501	Miniature WSB quick marking system; plain; Marker width 5 mm; 10 strips with 10 markers per card	5
248-501/000-002	Miniature WSB quick marking system; plain; Marker width 5 mm; 10 strips with 10 markers per card	5
248-501/000-005	Miniature WSB quick marking system; plain; Marker width 5 mm; 10 strips with 10 markers per card	5
248-501/000-006	Miniature WSB quick marking system; plain; Marker width 5 mm; 10 strips with 10 markers per card	5
248-501/000-007	Miniature WSB quick marking system; plain; Marker width 5 mm; 10 strips with 10 markers per card	5
248-501/000-012	Miniature WSB quick marking system; plain; Marker width 5 mm; 10 strips with 10 markers per card	5
248-501/000-017	Miniature WSB quick marking system; plain; Marker width 5 mm; 10 strips with 10 markers per card	5
248-501/000-023	Miniature WSB quick marking system; plain; Marker width 5 mm; 10 strips with 10 markers per card	5
248-501/000-024	Miniature WSB quick marking system; plain; Marker width 5 mm; 10 strips with 10 markers per card	5
750-100	Markers for group marker carrier; DIN A4 sheet (160 markers)	1
750-103	750/753 Series marker carrier	50


Accessories


General accessory

Item no.	Description	Pack. unit (Sub Pack)
210-719	Operating tool with partially insulated shaft; Type 1, blade (2.5 x 0.4) mm; suitable for 279, 726, 727, 2000, 2001 and 2020 series	1
210-720	Operating tool with partially insulated shaft; Type 2, blade (3.5 x 0.5) mm; suitable for 260, 261, 262, 264, 270, 280, 281, 290, 775, 776, 777, 769, 780, 781, 869, 870, 880, 2002, 2003, 2004, 2005 and 2022 Series	1
288-812	Power supply unit; with universal mounting carrier; AC 230 V / DC 24 V,; Output voltage indication	1
288-813	Power supply unit; with universal mounting carrier; AC 115 V / DC 24 V,; Output voltage indication	1
790-108	Shield clamping saddle; 11 mm wide; diameter of compatible conductor; up to 8 mm	10
790-116	Shield clamping saddle; 19 mm wide; diameter of compatible conductor; 7 mm to 16 mm	10
790-124	Shield clamping saddle; 27 mm wide; diameter of compatible conductor; 6 mm to 24 mm	10
790-140	Shield clamping saddle; 43 mm wide; diameter of compatible conductor; 22 mm to 40 mm	10

Images & drawings







Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.