

W WD SERIES



FEATURES

- 19" EIA 310-D Compliant
- 2 pair of #12-24 rails; fully adjustable
- The WD provides additional depth for larger pieces of equipment
- Solid Steel or Plexiglas Doors
- 1, 2, 3, and 4" conduit knockouts on top and bottom of rear section; 1, 2, 3, and 4" on rear section
- Pin hinges provide added strength for rear section
- Dust Kit available to protect equipment in high dust/industrial areas
- Weight tested to 1/2" of deflection

WD SERIES

PART NO.

DESCRIPTION

GL24WD	24"H x 24"W x 32.13"D, Usable depth 30", Maximum rail spacing 23", 11 RMU, Plexiglas door, Weight Capacity 250 lbs.*, Shipping wt. 125 lbs.
GL24WDS	Same as GL24WD except solid door
GL36WD	36"H x 24"W x 32.13"D, Usable depth 30", Maximum rail spacing 23", 18 RMU, Plexiglas door, Weight Capacity 300 lbs.*, Shipping wt. 150 lbs.
GL36WDS	Same as GL36WD except solid door
GL48WD	48"H x 24"W x 32.13"D, Usable depth 30", Maximum rail spacing 23", 25 RMU, Plexiglas door, Weight Capacity 350 lbs.*, Shipping wt. 200 lbs.
GL48WDS	Same as GL48WD except solid door

*All maximum weight capacities determined at minimal deflection.

ACCESSORIES

PART NO.

DESCRIPTION

7219	6 position Power Strip for 19" mounting; 5-15R receptacle and 5-15P plug
7219-SR14	14 position (6 front/8 back) Power Strip for 19" mounting; 5-15R receptacle and 5-15P plug with surge protector
7206-EIA	Stationary Shelf, 17.468"W x 18"D, 80 lb. weight capacity
7206-FR-AHD	Stationary Shelf (front/rear mount adjustable) 17.5"W x 22.25"D, 200 lb. weight capacity
7206-SL	Sliding Shelf, 16.343"W x 17.5"D, 40 lb. weight capacity
7206-FRSL-AHD	Sliding Shelf (front/rear mount adjustable) 17.5"W x 22"D, 110 lb. weight capacity
CBB-19	Copper Bus Bar for 19" mounting (isolated)
GR102	Grounding Kit for WM, WD, WS, and WE Wall Mounts
HDW-104-50	Package of 50 Pan Head Phillips #12-24 x 1/2" screws (Type 23, black)
7217WS	Fan Assembly with fan guards and two 75 CFM fans
FFK1	Four Fan Filters
DK1	Dust Resistant Kit (includes 4 cover plates, 4 fan filters and hardware)
7208WD	One Set of 5 Casters, 2 locking and 3 non-locking