



Shown with optional accessories

FEATURES

- 19" EIA 310-D Compliant
- Ideal size for areas where space is limited (e.g. classrooms and convenience stores)
- One pair of #10-32 rails
- Main body separates from back panel allowing for easy, one person installation
- Unique security bit required to remove main body from back panel
- "Spare" 1 RMU tab on back panel allows power strip mounting
- Solid Steel or Plexiglas Doors

15WM

PART NO.

GL15WM

DESCRIPTION

15.38"H x 22.25"W x 17.66"D, Usable depth 17", 7 RMU, Plexiglas Front Door, Weight Capacity 100 lbs., Shipping wt. 50 lbs.,

GL15WMS

15.38"H x 22.25"W x 17.66"D, Usable depth 17", 7 RMU, Solid Front Door, Weight Capacity 100 lbs., Shipping wt. 50 lbs.,

ACCESSORIES

PART NO.

7219

DESCRIPTION

6 position Power Strip for 19" mounting; 5-15R receptacle and 5-15P plug

7219-SR14

14 position (6 front/8 back) Power Strip for 19" mounting; 5-15R receptacle and 5-15P plug with surge protector

7219-20AR

6 position, 20 amp Power Strip for 19" mounting; 5-20R receptacle and 5-20P plug

7206-14

Stationary Shelf, 17.5"W x 14"D, 80 lb. weight capacity

CBB-19

Copper Bus Bar for 19" mounting (isolated)

GR102

Grounding Kit for use with WM, WS, WD and WE Wall Mounts

7217-04

Fan Kit (includes single 75 CFM fan with fan guards and power cord)