



NEMA 12 Wall Mount Enclosures have been independently tested and certified to meet the National Electrical Manufacturers Association's Type 12 standard. NEMA 12 enclosures are intended for indoor use to provide a degree of protection to the equipment inside the enclosure against dust, falling dirt, water and non-corrosive liquids.

FEATURES

- 19" EIA 310-D Compliant
- 2 pair of #12-24 rails; fully adjustable
- Reversible mounting
- Keyed locks with dust covers
- Front and rear sections lock independently
- Provisions for cable access for 1", 2", and 3" conduit knock-outs
- Provisions for fan assembly kit
- 14 gauge main body and rear section

NEMA 12 WALL MOUNT PART NO. DESCRIPTION

GL240N12	24"H x 24"W x 24"D, Rack Space 12 RMU, Wt. cap. 150 lbs., Shipping wt. 105 lbs.; can accept one FFKN12-A4
GL360N12	36"H x 24"W x 24"D, Rack Space 19 RMU, Wt. cap. 250 lbs., Shipping wt. 140 lbs.; can accept two FFKN12-A4
GL480N12	48"H x 24"W x 24"D, Rack Space 26 RMU, Wt. cap. 300 lbs., Shipping wt. 175 lbs.; can accept three FFKN12-A4

ACCESSORIES PART NO. DESCRIPTION

FFKN12-A4	Fan Assembly (includes filter) and exhaust filter, 38 CFM, 115V
FILTER-10	Package of five replacement filters for FFKN12-A4

