


N4WNSM 4 Channel NVR with Built-In Monitor
N8WNSM 8 Channel NVR with Built-In Monitor
N16WNSM 16 Channel NVR with Built-In Monitor



N4WNSM1TB	N8WNSM1TB	N16WNSM2TB
N4WNSM2TB	N8WNSM2TB	N16WNSM3TB
N4WNSM3TB	N8WNSM3TB	N16WNSM4TB
N4WNSM4TB	N8WNSM4TB	N16WNSM6TB
N4WNSM6TB	N8WNSM6TB	N16WNSM9TB
N4WNSM9TB	N8WNSM9TB	



Patented Design



Storage from 1TB up to 9TB

For the latest mobile apps
and CMS software go to:
www.specotech.com/DVRApps



Features

EZ Camera: quickly discovers and installs IP cameras

EZ Setup: for quick system setup

EZ Network: for quick set-up on a network

EZ Search: quickly search events from thumbnails

EZ Record: quickly setup recording resolutions and recording type

EZ Copy: auto copy what you are playing onto a USB flash drive

- Plug & play feature with Speco's OnSIP/IP cameras
- ONVIF support*
- Dual network ports for isolating IP camera network traffic and remote network
- Supports all H.264 compression profiles (baseline, main and high)
- A patented DVR solution that easily mounts in equipment closets or electrical rooms for covert installations
- Network video recorder with free DDNS server
- Easy and simple graphical user interface
- Built-in 7" monitor for viewing and control at the DVR
- Digital Deterrent® for triggering audio message via motion detection or sensor
- 2-way audio communication
- Programmable recording on motion detection, sensor, schedule, continuous and manual
- Full HD (1920 x 1080) recording and playback
- Supports wireless access point for viewing and configuration
- Built-in S.M.A.R.T. Technology (Self-Monitoring, Analysis and Reporting, Technology for HDD)
- 4/8/16 channel selectable local or IP camera audio recording
- Covert camera operation provides enhanced security and administrator control



EZ Set-Up Wizards!

One click wizard guides you to set up essentials of the system in a logical and easy to understand sequence.

- Date/Time • Recording method • Recording video quality • Network

- Password to secure installation authorization
- Easy firmware upgrade by USB port or network
- User Access: up to 4 concurrent users
- Remote monitoring / recording / playback / configuration / software upgrades and PTZ control via internet
- Supports multiple PC based browsers such as Internet Explorer, Google Chrome, Firefox and Safari
- Network accessible via SpecoTech Multi-Client Software, Secure Guard® CMS and Speco Player Mobile Viewer
- PC and MAC® compatible
- 3 year warranty
- Free Apps with support for view on iPhone®, iPad® or Android™
iPhone and Android are trademarks of Apple & Google respectively.

Specifications

Recording Resolutions: D1, 1280x720, 1920x1080
3 internal hard drives
4/8/16 channel audio input, 1 channel audio output
Motion detection, sensor, schedule, continuous and manual recording
Video Outputs: 1 HDMI, 1 VGA, 1 MAIN
USB 2.0 port for snapshot and video clip exporting
Multiple language on-screen menus

IR remote control included
Network software supports Static IP, DHCP and DDNS
Network hardware supports 10/100/1000Mbps
Power Requirement: 12VDC @ 5A
Operating Temperature: 41° F – 104° F
Dimensions: 13.5" (W) x 17" (H) x 3.5" (D)
Weight: 12 lbs.

Optional Accessory



IRRPTKIT
IR Repeater Kit



DSWFUSB
USB Wireless
Access Point

*visit www.specotech.com/onvif.html for latest ONVIF support

Speco Technologies is constantly developing and improving products.

We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 7/31/13

For more information contact Speco Technologies

200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com

N4WNSM / N8WNSM / N16WNSM Technical Specifications:
NS Plug & Play Wall Mount Network Video Recorder



Model		N4WNSM	N8WNSM	N16WNSM
Video	Input	IP Camera	4	8
		Resolution	Max. 1920 x 1080	
	Output	Main Monitor	VGA and HDMI	
		Sub Monitor	CVBS	
Audio	Input	IP Camera (network)	4	8
		Local Input (RCA)	4	8
	Output	Local Output (RCA)	1	
	Audio Codec		G.711	
Event	Sensor In	IP Camera (network)	4	8
		Local Input (terminal block)	4	
	Local Alarm Output (terminal block)		1	
	Motion Detection (from IP camera)		Yes	
Serial	RS-232C		1	
	RS-485		1	
Network	LAN (IP Camera, Auto Connection)		10/100 Base-T	10/100/1000 Base-T
	WAN (IP Camera, Remote Access)		10/100 Base-T	10/100/1000 Base-T
	Protocols		TCP/IP, UDP, DHCP, HTTP, NTP, SMTP, TRP, RTSP, ONVIF	
Recording	Compression		H.264 (baseline, main and high profile)	
	Resolution & Frame Rate	D1	120fps	240fps
		1280 x 720	120fps	240fps
		1920 x 1080	120fps	240fps
	Recording Mode		Continuous / Motion / Sensor / Schedule / Manual	
	Pre-Recording		Max. 20 minutes	
Post Recording		Max. 60 seconds		
Playback	Search		EZSearch, Date/Time, Event, Archive, Log	
	Multi-Decoding		1, 4	1, 4, 8
	Playback Speed		x0.25, x0.5, x2, x4, x8, x16, x32, x64	
Backup	Media		USB Drive, External HDD, Network	
	File Format		BMP, AVI, Proprietary Format	
	Large Backup		Yes (max. 24 hours)	
Storage	HDD	Capacity of 1 HDD	3TB	3TB
		Internal HDDs	3	
		e-SATA	1	
	USB		3	
User I/F	Input Method		IR, Mouse, Keyboard Controller	
Features	Digital Deterrent®		Up to 8 audio files	
	Dynamic DNS		Yes (free Speco DDNS)	
	Digital Zoom		Yes	
	DLS (day light savings)		Yes	
	NTP (network time protocol)		Yes	
	S.M.A.R.T		Yes	
	Internal Beep		Yes	
	Multi-Language		Yes	
E-mail Notification		Yes		
Network Access	Smartphone Viewer		iPad® / iPhone® / Android™	
	PC Web Viewer		Windows (IE, Chrome, Firefox, Safari)	
	PC Client		SpecoTech Multi-Client Viewer and Secure Guard® CMS	
	MAC Client		Speco Client for MAC and Secure Guard® CMS	
	Remote Setup and Upgrade		Yes	
Power	Power Supply Voltage		12VDC, 5A	
Temperature	Operating Temperature		41° F – 104° F / During Storage: 14° F – 122° F	
Weight	Unit Weight (gross weight)		12 lbs.	
Dimensions	Unit Dimensions (W x H x D)		13.5" (W) x 17" (H) x 3.5" (D)	

Please note that specifications and unit exterior design are subject to change without notification.

For more information contact Speco Technologies 200 New Highway, Amityville, NY 11701
Toll Free: 1-800-645-5516 Fax: 631-957-9142 or 631-957-3880 Website: www.specotech.com

Rev. 7/31/13

iPad, iPhone, iPod, iPod classic, iPod nano, iPod shuffle, and iPod touch are trademarks of Apple Inc., registered in the U.S. and other countries.