



VL7038IRVF 2.8-12mm auto iris varifocal lens
VL7039IRVF 6-50mm auto iris varifocal lens

Features

- 1/3" Sony™ Super-Had II™ CCD
- High Performance W-V DSP chip
- 600 TV lines resolution
- Multi-mount is a unique mount allowing installers to manipulate the camera to almost every angle with simplicity
- Zero noise and no ghosting effect with digital noise reduction (DNR)
- True day & night (ICR IR cut filter removable)
- External control rings for easy focus & distance adjustment
- Highest resolution: vivid, sharp picture in complete darkness
- Front glass heater: with thermic rays & built-in temperature sensor for immediate removal of condensation
- 5 year warranty




Specifications

Image Sensor 1/3" Sony Super-HAD II™ CCD
Resolution..... 600 TV lines
Minimum Illumination..... CDS off 0.15 lux, CDS on 0.00003 lux
Total Pixels 811 (H) x 508 (V)
Effective Pixels 768 (H) x 494 (V)
Number Of IR Leds..... 63
IR Range Up To 131'
White Balance ATW / Outdoor / Indoor / Manual
AWC (1,700°K - 11,000°K)
Gain Control High / Low / Off,
S/N Ratio More than 52dB (AGC off, Weight on)
Backlight Compensation..... HLC / BLC / Off
Electronic Shutter Speed..... 1/50, 1/60 sec. - 1/100,000 sec.
OSD..... Built-in
DNR..... Off / On (level adjustable)
D-WDR Indoor / Outdoor / Off
Sharpness 0-31' (level adjustable)
Privacy On / Off (12 zones)
Scanning System..... 2:1 interlace
Synchronization Internal
Day & Night Color / BW / Auto / EXT
Motion Detection..... On / Off (8 zones)

Sense-Up..... Off / Auto (selectable limit x2 - x256)
Mirror Off / Mirror / V-Rev / Rotate
Digital Zoom On (1x - 16x) / Off
Power Consumption 12VDC, 220mA (CDS off)
700mA (CDS on)
Heater on adj: 220-700mA
24VAC 150mA (CDS off)
450mA (CDS off)
Heater on adj: 170-450mA
Power Supply 12VDC / 24VAC (dual voltage)
(power supply not supplied)
Operating Temperature/
Humidity..... 14° F - 122° F / RH 95% max.
Storage Temperature/
Humidity..... -4° F - 140° F / RH 95% max.
Dimensions..... 5.4" (W) x 3.25" (H) x 11.5" (L)
Weight 4 lbs.

Optional Accessories



INTJBS
Square Junction Box



INTCM
Corner/Pole Adaptor



PSW4
Power Supply



PSW5
Power Supply