


960H Diamond Dome™ Series Miniature Indoor Camera

CDD11HW 3.6mm fixed lens, white housing

Features

- 1/3" Sony Super HAD II™ CCD
- 700 TV lines of resolution
- Unique and stylish housing for attractive indoor installation
- Small form factor for an unobtrusive look
- 3-axis wall or ceiling mount
- Full OSD operation
- 5 year warranty



Specifications

Image Sensor	1/3" Sony Super HAD II™ CCD
Resolution.....	700 TV lines
Minimum Illumination.....	Color: 0.1 lux, BW: 0.01 lux
Effective Pixels	976 (H) x 494 (V)
Total Pixels	1028 (H) x 508 (V)
Scanning System.....	2:1 interlace
Synchronization	Internal
OSD.....	Available
Backlight Compensation.....	BLC / HLC
S/N Ratio	More than 52dB
White Balance	ATW1 / ATW2 / ATW / Manual
Electronic Shutter Speed.....	Auto (1/60 sec. - 1/100,000 sec.)
2D-DNR.....	On / Off

WDR.....	DWDR
DPC.....	Auto / Manual / Off
Motion Detection.....	On / Off (4 zone)
Privacy.....	On / Off (8 zone)
Mirror	On / Off
Parking Line.....	Available
Sharpness	0 - 31 (level adjustable)
Day/Night.....	Auto / Color / BW / Ext
Power Supply	12VDC (power supply not included)
Power Consumption	200mA
Operating Temperature.....	14° F – 122° F
Dimensions.....	2.52" (H) x 2.87" (D)
Weight	4 oz.

Speco Technologies is constantly developing and improving products.
We reserve the right to modify product design and specifications without notice
and without incurring any obligation. Spec Rev. 1/20/14



Optional Accessory



PSW5
12VDC
Power Supply