

## Model 1052-HFHS-N

## Suspended Ceiling Enclosure

The Model 1052-HFHS-N wireless LAN access point enclosure is a locking 2' x 2' ceiling tile enclosure designed specifically for the Enterasys HiPath 3620/3640 802.11n access point. This aesthetic, white powder coated steel enclosure has mounting features on the door for installation of an aesthetic dual band MIMO antenna. No ceiling tile cuts are required for installation.



Model 1052-HFHS-N shown with Enterasys HiPath 3620 access point and MIMO dual band antenna (not included)

### Specifications:

- Ceiling tile enclosure specifically designed for Enterasys HiPath 3620/3640 access point
- UL50 listed and designed to meet NEC300-22 and 300-23 for plenum installations
- OSHPD approved OPA # 1638
- Mounting features on the door for dual band 802.11n antenna (Enterasys P/N WS-AI-DT04360 dual band 802.11n MIMO antenna, 3 X 36" pigtails with RP-SMA connectors)
- Back-box is 16 ga. galvanized steel. Door and flange are textured, white powder-coated steel
- Fully hinged locking door, keyed alike
- Size: Flange is 2' x 2', back-box is 12.5" x 12.5" x 4.0" deep
- Weight: 13lbs (not including access point or antenna)
- Enclosure must be supported by the building structure, independent of the suspended ceiling

### Model 1052-HFHS-N Includes:

- Access point mounting screws
- (4) Suspension wires
- (2) ¾" Trade conduit connectors for power and data cable openings in the back-box
- Mounting Instructions