

## Dry Moly Paste

### Dry film coating of molybdenum disulphide in paste form

#### Product Overview

ROCOL® Dry Moly Paste is a very high content molybdenum disulphide paste. It is designed to lubricate sliding mechanisms such as plain bearings, pins, cams and slides where a wet lubricant cannot be tolerated.

Also available in aerosol form – see Dry Moly Spray, and solvent based liquid form – see Dry Moly Fluid.

#### Typical Applications

- ROCOL Dry Moly Paste is an ideal assembly lubricant for disc spring assemblies, sliding mechanisms, plain bearings and other applications where a totally dry film lubricant is required.

#### Features and Benefits

- ROCOL Dry Moly Paste has a temperature range of -50°C to +450°C.
- ROCOL Dry Moly Paste can be used where wet films cannot be tolerated due to its dry film lubrication that resists pick up of contaminants.
- ROCOL Dry Moly Paste prevents galling, pick-up and seizure.
- ROCOL Dry Moly Paste is resistant to high loads (up to 7,000 kg/cm<sup>2</sup>).
- Excellent wear resistance due to its high molybdenum disulphide content.

#### Directions for Storage and Use

- Ensure surfaces to be treated are clean, dry and free from oil, grease or dirt contamination.
- Apply a thin even coating of ROCOL Dry Moly Paste by rubbing onto the surface with a lint free cloth.
- The applied film can be improved by lightly burnishing with a lint free cloth.
- ROCOL Dry Moly Paste is also available as Dry Moly Spray for application by aerosol, and Dry Moly Fluid for dipping, brushing or spraying.
- The storage temperature of ROCOL Dry Moly Paste should be controlled between +1°C and +40°C.
- Shelf life is 5 years from date of manufacture.

#### Specifications

ROCOL Dry Moly Paste meets the following specifications:

- Rolls Royce Specification – R-R OMAT 4/53

#### Pack Sizes

Pack Size	Part Code
100g	10040
750g	10046

## Dry Moly Paste

Dry film coating of molybdenum disulphide in paste form

Property	Test Method	Result
Appearance	Visual	Smooth blue-black paste
NLGI No.	IP 50 – ASTM D217	3
Base Type	N/A	Hydrocarbon blend
Solids	N/A	Molybdenum disulphide
Solids Content	N/A	50%
Temperature Range	N/A	-50°C to +450°C
Drop Point	IP 132	>100°C

Values quoted above are typical and do not constitute a specification.

### Safety Data Sheets

Safety data sheets are available for download from our website [www.rocol.com](http://www.rocol.com) or may be obtained from your usual ROCOL contact.

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.

Issue: 1 Date: 01-11

T +44 (0) 113 232 2600  
F +44 (0) 113 232 2740  
E [customer-service@rocol.com](mailto:customer-service@rocol.com)  
[www.rocol.com](http://www.rocol.com)

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67  
Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of  Ltd



BS EN ISO 9001  
Certificate No. FM 12448



BS EN ISO 14001  
Certificate No. 085 67396



OHSA 18001  
Certificate No. 095 78177



INVESTORS  
IN PEOPLE