

Product information

OpenOCTOPUS Fast Ethernet - OCTOPUS 8M

Industrial Ethernet:Waterproof IP67/IP54 Switches:OpenOCTOPUS:OpenOCTOPUS Fast Ethernet

<http://e-catalog.hirschmann.com/link/57078-24455-49850-351255-400977/en/OS20-000800T5T5TAMPHH08.0/uistate>

Name	
OpenOCTOPUS Fast Ethernet	
	
Managed IP 65 / IP 67 switch in accordance with IEEE 802.3, store-and-forward-switching, software layer 2 Professional, electrical Fast-Ethernet (10/100 MBit/s) M12-ports	
Delivery informations	
Availability	available
Product description	
Description	Managed IP 65 / IP 67 switch in accordance with IEEE 802.3, store-and-forward-switching, software layer 2 Professional, electrical Fast-Ethernet (10/100 MBit/s) M12-ports
Port type and quantity	8 ports in total; uplink ports: 10/100 BASE-TX, M12 "D"-coding, 4-pole; 8 x 10/100 BASE-TX; TP-cable, auto-crossing, auto-negotiation, auto-polarity.
Type	OCTOPUS 8M
Order No.	943 931-001
More Interfaces	
Power supply/signaling contact	1 x M12 5-pin connector, A coding, 1 x M12 5-pin connector, A coding
V.24 interface	1 x M12 4-pin connector, A coding
USB interface	1 x M12 5-pin socket, A coding
Network size - length of cable	
Twisted pair (TP)	0 - 100 m
Network size - cascading	
Line - / star topology	any
Ring structure (HIPER-Ring) quantity switches	50 (reconfiguration time < 0.3 sec.)
Power requirements	
Operating voltage DC	24/36/48 VDC -60% / +25% (9,6..60 VDC)
Current consumption at 48 V DC	100 mA
Software	
Management	Serial interface V.24 web-interface, Telnet, SSHv2, HTTP, HTTPS, TFTP, SFTP, SNMP v1/v2/v3, Traps
Diagnostics	LEDs (power 1, power 2, link status, data, redundancy manager, error) cable tester, signalling contact, RMON (statistics, history, alarms, events), SysLog support, port mirroring
Configuration	Command Line Interface (CLI), auto-configuration adapter, TELNET, BootP, DHCP Option 82, HiDiscovery
Security	Port Security (IP and MAC), SNMPv3, SSHv3, SNMP access settings (VLAN/IP), IEEE 802.1X authentication
Redundancy functions	redundant power supply
Other services	4 QoS queues, user priority (IEEE 802.1D/p), VLAN (IEEE 802.1Q), unknown multicast filtering, multicast support (IGMP Snooping/Querier, GMRP), broadcast limiter per port, ingress and egress packet limiter, Flow Control IEEE 802.3x, LLDP (topology discovery IEEE 802.1AB), Link Aggregation (IEEE 802.3ad), buffered real-time clock, PTP support (Precision Time Protocol) (IEEE 1588 client for system clock only), SNTP support (Simple Network Time Protocol, client/server)
Ambient conditions	
Operating temperature	-40 °C ... 70 °C
Storage/transport temperature	-40 °C ... 85 °C
Relative humidity (also condensing)	10 % ... 100 %
MTBF	27.6 years; MIL-HDBK 217F: Gb 25 °C
Mechanical construction	
Dimensions (W x H x D)	184 mm x 189 mm x 70 mm
Mounting	Wall mounting
Weight	1300 g
Protection class	IP65, IP67
Mechanical stability	
IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks

Industrial Ethernet: Waterproof IP67/IP54 Switches: OpenOCTOPUS: OpenOCTOPUS Fast Ethernet
<http://e-catalog.hirschmann.com/link/57078-24455-49850-351255-400977/en/OS20-000800T5T5TAMPHH08.0/uistate>

IEC 60068-2-6 vibration	1 mm, 2 Hz-13.2 Hz, 90 min.; 0.7 g, 13.2 Hz-100 Hz, 90 min.; 3.5 mm, 3 Hz-9 Hz, 10 cycles, 1 octave/min.; 1 g, 9 Hz-150 Hz, 10 cycles, 1 octave/min
EMC interference immunity	
EN 61000-4-2 electrostatic discharge (ESD)	4 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m (80-1000 MHz)
EN 61000-4-4 fast transients (burst)	2 kV power line, 1 kV data line
EN 61000-4-5 surge voltage	power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line
EN 61000-4-6 conducted immunity	3 V (10 kHz-150 kHz), 10 V (150 kHz-80 MHz)
EMC emitted immunity	
FCC CFR47 Part 15	FCC 47 CFR Part 15 Class A
EN 55022	EN 55022 Class A
Approvals	
Basis Standard	CE, C-Tick
Safety of industrial control equipment	cUL 508, GOST-R, CCC
Scope of delivery and accessories	
Scope of delivery	M12-connector (ELWIK 5012 PG7) for power connection, description and operating instructions
Note	Please note that some recommended accessory parts only support a temperature range from -25 °C to +70 °C and might limit the possible operating conditions for the entire system.
Accessories to order separately	M12 connector, "D"-coded (934 445-001); 2 m cordset with M12-connector, "D"-coded (934 578-001); 5 m cordset with M12-connectors, "D"-coded (934 578-002); 10 m cordset with M12-connectors, "D"-coded (934 578-003); Bulkhead M12 "D"-coded to RJ45 (934 498-001); OCTOPUS dust cover set (25 pieces) (942 057-001). OCTOPUS terminal cable (943 902-001), Autokonfigurationsadapter ACA21-M12 EEC (943 913-002)

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.