

Waterproof Color Camera with 60 Ft. Cable

CVC620WP 3.6mm wide angle lens, black housing

Features

- Completely waterproof with underwater operation capabilities to a maximum depth of 60'
- Nitrogen filled housing protects internal components
- 60' cable and mounting bracket included
- RoHS compliant
- 5 year warranty



Specifications

Image Sensor	1/4" color CCD
Resolution.....	350 TV lines
Minimum Illumination.....	1.0 lux
Effective Pixels	510 (H) x 492 (V)
Electronic Shutter Speed.....	Auto: 1/60 sec. - 1/100,000 sec.
Synchronization	Internal
Interlace	2:1
S/N Ratio	More than 46dB
Video Output Level	1.0Vp-p / 75 ohms
Scanning Frequency	15.75kHz (H) / 60Hz (V)
Scanning System	EIA standard 525 TV lines 60 fields/sec.
Maximum Operating Depth	60' underwater
Power Consumption	100mA
Power Requirements	12VDC (UL & CSA listed power supply included)
Operating Temperature/ Humidity.....	- 20° F – 120° F / within 95% RH
Dimensions.....	2.5" (L) x 1.5" (Dia.) x 3.5" (H)
Weight	9.8 oz.
Housing	Brass
Cable	60' of power/video cable included



Speco Technologies is constantly developing and improving products.
We reserve the right to modify product design and specifications without
notice and without incurring any obligation.
Spec Rev. 2/12/14