




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.





FOUR CABLE ASSEMBLIES P/N RCISC072-35A/N

PANDUIT PART NUMBER	WEIGHT
TPK2A32R88S68	6.13 lb (2781.6 g)

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS.
- MATERIAL:
PANEL HOUSING: STEEL
MODULAR JACKS: THERMOPLASTIC RESIN UL94V-0
- 32 PORT ANGLED PATCH PANEL 8 POSITION 8 WIRE.
- THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS AND WILL ACCEPT THREE OR FOUR PAIR MODULAR PLUGS WITHOUT DAMAGE.
- FOUR (4) 12-24 X 1/2" AND FOUR (4) M6X1X15MM ROUND HEAD SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- TPK2A32R88S68 KIT IS COMPRISED OF ANGLED PATCH PANEL ASSEMBLY TPA32R88S68Y AND 4 X 6 FT LONG CABLE ASSEMBLIES WITH HD68 CONNECTOR ON ONE END AND VHD68 CONNECTOR ON THE OTHER END. HD68 CONNECTOR PROVIDED WITH #4-40 LOCK SCREWS, VHD68 CONNECTOR PROVIDED WITH M2 LOCK SCREWS.

MODEL FILENAME	SIZE
DRAWING FILENAME	A
M02245BN_DC19/00A	
SCSI ANGLED PATCH PANEL KIT CUSTOMER DRAWING	
 TINLEY PARK, IL 60487	I.I. NUMBER
	PRODUCT SPEC/ PKG SPEC
	ASSY METHOD/ TEST METHOD
 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ± 1°
SCALE	.25:1
DRAWN BY BJN	REVIEW DRAWING NUMBERS
DATE 3-1-11	PART NO. TPK2A32R88S68
CHK'D MBVE	DRAWING NO. 02245-19

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	3-1-11	BJN	MBVE	RELEASED TO PRODUCTION	02245-19		RDE		