



VZ-PRO-16 ADVANTAGES

- Up to 16 Full HD video inputs and outputs
- Simultaneous 1080p video playback support
- Spectacular Ultra HD(4K) support for outstanding visual experiences
- Content management software
- Designed to operate 24/7/365 in mission-critical installations
- Industrial grade high-performance systems based on Intel® Xeon® CPU Windows® 7 Professional
- Max bit rate - 400Mbps (16 channel)

MODEL #	VZ-PRO-16
SPECIFICATIONS	
Processor	Intel® Xeon® E5 series processor
Storage	2 x 3.5" 500GB HDD
RAM	8GB DDR ECC (option: 16GB available)
Graphic	2 x VIA uH8 PCI-E graphics card
RESOLUTION	
Per Channel / Display	Up to 1920 x 1080
INTERFACE	
DVI (via VHDCI) Input	16 ea
HDMI (via VHDCI) Output	16 ea (DVI Option)
USB	2 ea
PS/2	2 ea
Serial Port	1 ea
Network (RJ-45)	2 ea - 10/100/1000 Base-T
GENERAL	
Power Supply	2 x 920W PSU; Power Input: 100 - 240V AC
Operating Temperature	41 ~ 95°F / 5 °C ~ 35°C
Operating Humidity	10 % - 90 % (Non-condensing)
Dimensions (W x D x H)	17.2" x 25.5" x 5.2" / 437 x 648 x 132 mm
Net Weight	54.4 lbs / 24.67 Kg

Contact ViewZ

- Address : 177 W. Orangethorpe Ave., Placentia, CA 92870
- Phone : (714) 996-1177, Fax : (714) 996-1138
- Sales : sales@viewzusa.com
- Specification subject to change without notice.

PRO-16 CONNECTION DIAGRAM

