

# Compact & Highly Efficient

## 16CH/8CH H.264 Digital Video Recorder



16CH/8CH CIF Real-time H.264 Digital Video Recorder

# SRD-1640/840



The SRD-1640 16CH and SRD-840 8CH are standalone DVRs that feature high recording quality CIF video in real time across all channels. Each channel can be configured to record quality and privacy masking separately. In addition, they provide versatile options for web access and remote monitoring using a PC or smartphone, making anytime, anywhere monitoring possible.

- 16CH/8CH CIF real-time DVR
- CIF resolution real-time recording capability (4CIF recording available)
- Compact product footprint
- Up to 480 (NTSC) / 400 (PAL)fps recording rate : SRD-1640  
240 (NTSC) / 200 (PAL)fps recording rate : SRD-840
- 4CH audio inputs and 1CH audio output
- SATA I/F HDD support (Internal Max. HDD x 1)
- Smart phone support
- Splits and exports small parts of a recorded video – Brightness and Contrast control via SmartViewer (SRD-1640)

# 16CH/8CH CIF Real-time H.264 Digital Video Recorder

## SRD-1640/840




### Specifications

		SRD-1640	SRD-840
DISPLAY			
Video	Inputs	16 composite video 0.5–1 Vpp, 75 ohm	8 composite video 0.5–1 Vpp, 75 ohm
	Resolution	704 x 480 NTSC, 704 x 576 PAL	
	Frame Rate	480fps NTSC, 400fps PAL	240fps NTSC, 200fps PAL
Live	Resolution	704 x 480 NTSC, 704 x 576 PAL	
	Multi Screen Display	1 / 4 / 6 / 8 / 9 / 16 / SEQUENCE / PIP	1 / 4 / 6 / 8 / SEQUENCE / PIP
PERFORMANCE			
Operating System	Embedded	Linux	
	Compression	H.264	
Recording	Record Rate (NTSC)	Up to 120fps @ 704 x 480	Up to 60fps @ 704 x 480
		Up to 240fps @ 704 x 240	Up to 120fps @ 704 x 240
		Up to 480fps @ 352 x 240	Up to 240fps @ 352 x 240U
	Record Rate (PAL)	Up to 100fps @ 704 x 576	Up to 50fps @ 704 x 576
		Up to 200fps @ 704 x 288	Up to 100fps @ 704 x 288
		Up to 400fps @ 352 x 288	Up to 200fps @ 352 x 288
Mode	NTSC : Manual, Schedule (Continuous/Event), Event (Pre/Post)		
	PAL : Manual, Schedule (Continuous/Event), Event (Pre/Post)		
Search & Playback	Overwrite Modes	Continuous	
	Pre-alarm	Up to 5sec (1, 2, 3, 4, 5sec)	
	Post-alarm	Up to 6 hour (5,10, 20, 30sec,1, 3, 5, 10, 20min, 1, 2, 3, 4, 5, 6hour)	
	Editing Function- Software	Contrast, brightness and color editing on live and recorded videos (SRD-1640)	
	Search Mode	Date/time, Event, Back up, Motion, POS	
	Playback Function	Fast forward / backward (2x, 4x, 8x, 16x, 32x, 64x) *Backward play with I-frame only	
Slow forward / backward (1/2x, 1/4x, 1/8x)			
Step forward / backward (2x, 4x, 8x, 16x, 32x, 64x) *Backward play with I-frame only			
Network (IPv4)	Transmission Speed	CIF 120/100fps	
	Bandwidth	Up to 4Mbps, Unlimited (4M) / 2 / 1.5 / 1Mbps / 800 / 600 / 500 / 400 / 300 / 200 / 100 / 50kbps	
	Bandwidth Control	Automatic	
	Stream	H.264 (CIF)	
	Max. Remote Users	4 Persons (Search up to (2), Live Unicast/Live Multicast available)	
	Protocol Support	TCP/IP,DHCP,PPPoE, SMTP, NTP, HTTP, DDNS, RTP, RTSP	
Smart Phone	Monitoring	Webviewer, CMS (Smart viewer, NET-i)	
	Platform	Android, iOS	
	Protocol support	RTP,RTSP, HTTP, CGI	
	Remote users Maximum	Live(1)	
	Internal HDD	Up to 1 SATA HDDs	
	USB (Back-up)	2 USB Ports	
Storage	File Format (Back-up)	BU (DVR Player), EXE (Include Player)	
	Password Protection	1 Admin, 10 Group, 10 User per 1 Group	
Security	Data Authentication	Watermark	
	INTERFACE		
Monitors	VGA	1 VGA (1024 x 768) *Main Composite Selectable	
	HDMI	Not Support	
	Main/Spot Composite	1 BNC (1 Vp-p, 75 ohm)/Analog Spot (1 BNC, 1 Vp-p, 75 ohm) Selectable	
	Spot Composite	Analog Spot (1 BNC, 1 Vp-p, 75 ohm)	
Audio	Loop Outputs	Not Support	
	Inputs / Output	4 line in / 1 line out	
	Compression	G.711	
	Sampling Rate	8KHz	
Alarm	Inputs / Output	Terminal 16 inputs (NO/NC) / Terminal 2 relay outputs (NO/NC), Rating : 24VDC/1A, 125V AC/0.5A	Terminal 8 inputs (NO/NC) / Terminal 2 relay outputs (NO/NC), Rating : 24VDC/1A, 125V AC/0.5A
	Remote Notification	Notification via e-mail	
Connections	Ethernet	1 RJ45 10/100 Base-T	
	Serial Interface	RS-485(Half) for PTZ, System Keyboard *Support for POS Interface (VSI-Pro)	
	USB	USB 2.0, 2 ports (Front)	
	Application Support	Mouse, Remote Controller	
GENERAL	Protocol Support	Samsung-E/ Samsung-T/ Pelco-D/ Pelco-p/Panasonic/ Phillips/ AD/ DIAMOND/ ERNA/ KALATEL/ VCL TP/VICON/ ELMO	
	Electrical	Input Voltage / Current	DC12V Adaptor,4A,100~250VAC, 50~60Hz, 36watt
Environmental	Power Consumption	Normal 15W (with 1x HDD)	
	Operating Temperature / Humidity	+0°C ~ +40°C (+32°F ~ +104°F) / 20%RH ~ 85%RH	
Mechanical	Dimensions (WxHxD)	360 x 44 x 159.9 mm (14.17" x 1.73" x 6.30")	
	Weight (With hard disks)	1.72kg (3.79lb)	1.68kg (3.70lb)
Language	RACK MOUNT KIT	Not Support	
		Korean, Japanese, Chinese, English, French, German, Spanish, Italian, Russian, Polish, Czech, Turkish, Netherlands, Portuguese, Swedish, Danish, Thai, Rumanian, Serbian, Croatian, Hungarian, Greek (22 Language)	

### Dimensions

Unit : mm (inch)



Design and specifications are subject to change without notice.

■ DISTRIBUTED BY



SAMSUNG TECHWIN AMERICA Inc.  
100 Challenger Rd. Suite 700 Ridgefield Park, NJ 07660  
Toll Free : +1-877-213-1222 Direct : +1-201-325-6920  
Fax : +1-201-373-0124  
www.samsungcctvusa.com



The Eco mark represents  
Samsung Techwin's will to create  
environment-friendly products, and indicates  
that the product satisfies the EU RoHS Directive.