

M12 Rugged Distribution Boxes, One Signal Per Socket, On-Board M23 Connection, with or without LED

ASBS-R 4 5-4 | ASBS-R 8 5-4


ASBS-R 4/LED 5-4 | ASBS-R 8/LED 5-4




4- and 8-Ports

ASBS-R pluggable actuator/sensor distributor, 4 or 8 x M12 ports, 4-poles, with LED operating and function display, one signal per socket, ground connection, M23 connection for the control cable, 12-poles

4-Ports




8-Ports




Pin Assignments

M12 Wiring Diagrams

4-Ports



8-Ports





M12 Rugged Distribution Boxes, One Signal Per Socket, On-Board M23 Connection, with or without LED

Technical Data

Environmental Conditions

Degree of protection	IP65 / IP67
Pollution severity	3
Operating temperature range	-40°C / +80°C (dragchain and UL max. 60°C)

Materials

Contact	CuZn, pre-nickel and gold-plated
Contact bearer	TPU-GF
Housing	Zinc die casting
O-ring	FKM



Electrical Data

Rated voltage	30 V
Rated current*	4 A per outlet / 12 A max. total; at 40°C
Rated impulse voltage	32 V
Contact resistance	≤5mΩ
Insulation resistance	> 10 ⁹ Ω

* only in locked position with its proper counterparts or dust covers

Additional Technical Data

operation display: LED Green
Function display / channel status:
LED Channel A: Yellow

Part Number		Ports	Characteristics
ASBS-R 4 5-4	ASBS-R 4/LED 5-4	4	UL     
ASBS-R 8 5-4	ASBS-R 8/LED 5-4	8	UL 