




## Accessories

Canovate offers a wide range of accessories to provide the best cable management and installation options for the complex requirements of IT users. Canovate believes that a proper and safe cabling is a real challenge for the installers and thus we try to offer the best variety to satisfy all their requirements

# Accessories


## 19" Cantilever Shelf



**Material** 1,5 mm Steel **Maximum Static Load** 15-25 kg  
**Finish** Electrostatic Powder Paint **Packaging** Bubble Nylon

H (U)	D (mm)	W (mm)	Inner W (mm)	Weight kg	Part No
1U	150	483	437	0,84	CCA-X-1001
2U	250	483	437	1,58	CCA-X-1002
2U	400	483	437	2,43	CCA-X-1003


## 19" Heavy Duty Fixed Shelf



**Material** 1,5 mm Steel **Maximum Static Load** 100 kg  
**Finish** Electrostatic Powder Paint **Packaging** One piece in a box

H (U)	D (mm)	W (mm)	Inner W (mm)	Weight kg	Part No
1U	400	483	435	2,95	CCA-X-1008
1U	600	483	435	3,95	CCA-X-1009
1U	800	483	435	4,95	CCA-X-1010
1U	1000	483	435	5,95	CCA-X-1011


## 19" Drawer



**Material** 1,5 mm Steel **Maximum Static Load** 35 kg  
**Finish** Electrostatic Powder Paint **Packaging** Bubble Nylon

H (U)	D (mm)	W (mm)	Inner W (mm)	Weight kg	Part No
2U	500	483	435	6,36	CCA-X-1016
3U	500	483	435	9,54	CCA-X-1017


## 19" 1U Fan Module



**Fan Speed** 2700 - 3100 rpm **Packaging** One piece in a box  
**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint  
**Air Flow** 95 - 115 CFM **Noise** 44 - 49 dB (A)  
**Operating Voltage** AC 220 - 240 Volts 50/60 Hz  
**Standards** Conforms to IEC 297-1

H (U)	D (mm)	W (mm)	Number of Fans	Weight kg	Part No
1U	258	483	3	4,19	CCA-X-2001


## 19" Fixed Shelf



**Material** 1,0 mm Steel **Finish** Electrostatic Powder Paint  
**Maximum Static Load** 50 kg **Packaging** One piece in a box

H (U)	D (mm)	W (mm)	Inner W (mm)	Weight kg	Part No
1U	400	465	465	1,22	CCA-X-1004
1U	600	465	465	1,83	CCA-X-1005
1U	800	465	465	2,44	CCA-X-1006
1U	1000	465	465	3,05	CCA-X-1007


## 19" Sliding Shelf



**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint  
**Maximum Static Load** 35 kg **Packaging** One piece in a box

H (U)	D (mm)	W (mm)	Inner W (mm)	Weight kg	Part No
1U	400	483	435		CCA-X-1012
1U	600	483	435	3,56	CCA-X-1013
1U	800	483	435		CCA-X-1014
1U	1000	483	435		CCA-X-1015


## Fan Module for Wall Mount Enclosures



**Material** 0,8 mm Steel  
**Finish** Electrostatic Powder Paint **Air Flow** 95 - 115 CFM  
**Operating Voltage** AC 220 - 240 Volts 50/60 Hz  
**Noise** 44 - 49 dB (A) **Standards** Conforms to IEC 297-1  
**Packaging** One piece in a box **Fan Speed** 2700 - 3100 rpm

H (mm)	D (mm)	W (mm)	Number of Fans	Weight kg	Part No
39	135	326	1	1,27	CWA-X-2001
39	135	326	2	1,80	CWA-X-2002

## Fan Module for inorax-ST series




**Material** 0,8 mm Steel **Fan Speed** 2700 - 3100 rpm  
**Air Flow** 95 - 115 CFM **Finish** Electrostatic Powder Paint  
**Operating Voltage** AC 220 - 240 Volts 50/60 Hz  
**Noise** 44 - 49 dB (A) **Packaging** One piece in a box  
**Standards** Conforms to IEC 297-1

H (mm)	D (mm)	W (mm)	Number of Fans	Weight kg	Part No
47	375	363	2	2,90	CSA-X-2001
47	375	363	4	3,95	CSA-X-2002

\* X : Color code = 7: RAL 7035 (Grey); 9: RAL 9005 (Black)

# Accessories


## Fan Module for inorax-AI Series



**Operating Voltage** AC 220 - 240 Volts 50/60 Hz  
**Standards** Conforms to IEC 297-1 **Finish** Electrostatic Powder Paint  
**Material** 1,5 mm Steel **Air Flow** 95 - 115 CFM **Noise** 44 - 49 dB (A)  
**Fan Speed** 2700 - 3100 rpm **Packaging** One piece in a box

H (mm)	D (mm)	W (mm)	Number of Fans	Weight kg	Part No
47	375	363	2	3,76	CPA-X-2001
47	375	363	4	4,81	CPA-X-2002
47	510	363	6	6,74	CPA-X-2003

## 19" 1U Plastic Blanking Panel



**Material** Plastic ABS **Packaging** One piece in a box

H (U)	W (mm)	D (mm)	Weight kg	Part No
1U	6	6	0,08	CCA-X-4001

## 19" Plastic Cable Organizer



**Material** 1,5 mm Steel, Plastic **Packaging** One piece in a box **Finish** Electrostatic Powder Paint

H (U)	W (mm)	D (mm)	Weight kg	Part No
1U	483	80	0,49	CCA-0-5001


## 19" Covered Cable Organizer



**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint  
**Packaging** One piece in a box

H (U)	W (mm)	Weight kg	Part No
1U	483	0,6	CCA-X-5004


## Vertical Side Cable Organizer Type1



**Material** 1,5 mm Steel **Finish** Zinc Plated  
**Packaging** 2 pieces in Bubble Nylon

H (U)	H (mm)	D (mm)	W (mm)	Weight kg	Part No
26U	1246	10	260	3,20	CCA-0-5011
32U	1510	10	260	3,86	CCA-0-5012
36U	1686	10	260	4,36	CCA-0-5013
39U	1820	10	260	4,74	CCA-0-5014
42U	1950	10	260	5,11	CCA-0-5015
47U	2170	10	260	5,74	CCA-0-5016


## Plinth for inorax



**Material** 2 mm Steel **Packaging** One piece in a box  
**Finish** Electrostatic Powder Paint

H (mm)	D (mm)	W (mm)	Weight kg	Part No
90	600	600	5,95	CCA-X-3001
90	600	800	7,10	CCA-X-3002
90	600	1000	7,96	CCA-X-3003
90	600	1100	8,83	CCA-X-3004
90	600	1200	9,71	CCA-X-3005
90	800	800	7,27	CCA-X-3006
90	800	1000	8,14	CCA-X-3007
90	800	1100	9,01	CCA-X-3008
90	800	1200	9,89	CCA-X-3009

## 19" Blanking Panels



**Material** 1,2 mm Steel **Finish** Electrostatic Powder Paint  
**Packaging** One piece in a box

H (U)	W (mm)	D (mm)	Weight kg	Part No
1U	483	9	0,26	CCA-X-4002
2U	483	9	0,46	CCA-X-4003
4U	483	9	0,86	CCA-X-4004

## 19" Ventilated Blanking Panels



**Material** 1,2 mm Steel **Finish** Electrostatic Powder Paint  
**Packaging** One piece in a box

H (U)	W (mm)	D (mm)	Weight kg	Part No
1U	483	9	0,24	CCA-X-4005
2U	483	9	0,42	CCA-X-4006


## Cable Hook



**Material** Steel **Finish** Zinc Plated **Packaging** 1 Pc in a Nylon

H (mm)	W (mm)	D (mm)	Weight kg	Part No
100	60	100	0,09	CCA-0-5002
170	60	80	0,10	CCA-0-5003

## Vertical Side Cable Organizer Type2





**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint  
**Packaging** 2 pieces in a box

H (U)	H (mm)	D (mm)	W (mm)	Weight kg	Part No
26U	1246	10	260	3,00	CCA-X-5017
32U	1510	10	260	3,61	CCA-X-5018
36U	1686	10	260	4,01	CCA-X-5019
39U	1820	10	260	4,44	CCA-X-5020
42U	1950	10	260	4,79	CCA-X-5021
47U	2170	10	260	5,38	CCA-X-5022

\* X : Color code = 7: RAL 7035 (Grey); 9: RAL 9005 (Black)

# Accessories

## Modular Adjustable Vertical Cable Organizer Type1




**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint  
**Packaging** 1 piece in a box **Module Capacity** Max 10 pieces  
**Mounting Back Plane**

H (U)	D (mm)	W (mm)	Weight kg	Part No
42U	13	120	2,83	CCA-X-5023
47U	13	120	3,17	CCA-X-5024

### Module

H (mm)	D (mm)	W (mm)	Weight kg	Part No
150	70	90	0,42	CCA-X-5025


## Vertical Cable Organizer



**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint  
**Packaging** 2 pieces in a box

H (U)	D (mm)	W (mm)	Weight kg	Part No
26U	92	100	3,80	CCA-X-5005
32U	92	100	4,10	CCA-X-5006
36U	92	100	4,70	CCA-X-5007
39U	92	100	5,10	CCA-X-5008
42U	92	100	5,50	CCA-X-5009
47U	92	100	6,20	CCA-X-5010

## 19" 1U Light



**Material** Anodized Aluminum Extrusion **Power Consumption** 11W  
**Packaging** One piece in a box **Finish** Electrostatic Powder Paint  
**Voltage** AC 220 - 240 Volts 50/60 Hz

Length (U)	D (mm)	W (mm)	Weight kg	Part No
400	15	24	0,25	CCA-0-7025


## Cable Clamp for C-Rail



**Material** Steel  
**Finish** Zinc Plated  
**Packaging** 5 Pieces in a box

Cable Diameter mm	Weight kg	Part No
8 - 12	0,042	CCA-0-5041
11 - 18	0,048	CCA-0-5042
12 - 23	0,054	CCA-0-5043


## 19" Cable Entry



**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint  
**Packaging** One piece in a box

H (U)	D (mm)	W (mm)	Weight kg	Part No
1U	9	483	0,16	CCA-X-5029
2U	9	483	0,25	CCA-X-5030


## 19" Cable Entry with Brush



**Material** 1,5 mm Steel, Brush **Finish** Electrostatic Powder Paint  
**Packaging** One piece in a box

H (U)	D (mm)	W (mm)	Weight kg	Part No
1U	10	483	0,2	CCA-X-5031
2U	10	483	0,3	CCA-X-5032


## 19" 1U Light



**Material** 1,2 mm Steel **Finish** Electrostatic Powder Paint  
**Packaging** One piece in a box **Power** 11W  
**Voltage** AC 220 - 240 Volts 50/60 Hz

H (U)	D (mm)	W (mm)	Weight kg	Part No
1U	53	483	0,5	CCA-X-7001


## Cable Clamp Rail



**Material** 1,5 mm Steel **Finish** Zinc Plated  
**Packaging** One piece in a box

Length (mm)	H (mm)	W (mm)	Weight kg	Part No
600	64	15	0,36	CCA-0-5033
800	64	15	0,48	CCA-0-5034
1000	64	15	0,60	CCA-0-5035
1200	64	15	0,72	CCA-0-5036

## C-Rail




**Material** Anodized Aluminum Profile  
**Finish** Anodization  
**Packaging** One piece in a box

Length (mm)	H (mm)	W (mm)	Weight kg	Part No
600	20	34	0,30	CCA-0-5037
800	20	34	0,39	CCA-0-5038
1000	20	34	0,49	CCA-0-5039
1200	20	34	0,59	CCA-0-5040

\* X : Color code = 7: RAL 7035 (Grey); 9: RAL 9005 (Black)

# Accessories

## Chassis Rail



**Material** 2 mm Steel **Finish** Zinc Plated

**Packaging** 2 pieces in a box

Length (mm)	H (mm)	W (mm)	Weight kg	Part No
600	1,9	3,3	0,47	CCA-O-7002
800	1,9	3,3	0,63	CCA-O-7003
1000	1,9	3,3	0,79	CCA-O-7004

## Integral Console + KVM



Integral console controls computers and servers inside cabinets or server room with one LCD monitor, keyboard and mouse. This prevents unnecessary costs and saves space.

Sliding rail mount reduces occupied space inside cabinets.

8 or 16 computers can be connected. Daisy chain structure provides 3 level cascade connection and controllability up to 999 computers.

### Technical Specifications

17"/19" TFT LCD Display

8/16 Port KVM Switch

On Screen Display

Hot Key Function

Hot Plug Function

LCD Panel Size	Connection Type	8 Port	Part 16 Port
17"	USB	CCA-O-8001	CCA-O-8005
17"	PS/2	CCA-O-8002	CCA-O-8006
19"	USB	CCA-O-8003	CCA-O-8007
19"	PS/2	CCA-O-8004	CCA-O-8008

## Baying Kit for inorax-AI Series



**Material** 2 mm Galvanized Steel

**Packaging** 4 pieces in a set

H (mm)	D (mm)	W (mm)	Weight kg	Part No
10	66	50	0,055	CPA-O-7001

## Stabilizer for Ceiling




**Material** 1,5 mm Steel **Finish** Zinc Plated

**Set** Kit includes 4 pcs vertical profiles and 2 pcs ceiling fixing profiles, bolts

Cabinet D (mm)	H (mm)	Part No
300 (ETSI)	1000	CCA-O-7005
600	1000	CCA-O-7006
800	1000	CCA-O-7007
1000	1000	CCA-O-7008
1200	1000	CCA-O-7009

\* X : Color code = 7: RAL 7035 (Grey); 9: RAL 9005 (Black)

## Sliding Anti-Swing Stabilizer



**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint

**Packaging** 1 piece in a set

H (mm)	D (mm)	W (mm)	Weight kg	Part No
90	600	1000	9,47	CPA-X-3019
90	600	1100	10,50	CPA-X-3020
90	600	1200	11,64	CPA-X-3021
90	800	800	11,70	CPA-X-3022
90	800	1000	12,63	CPA-X-3023
90	800	1100	14,01	CPA-X-3024
90	800	1200	15,28	CPA-X-3025

## Earthing Kit



**Material** Copper **Finish** PVC Jacket

**Packaging** One set in a box **Packaging** 4 pcs

Length (mm)	Cross Section	Weight kg	Part No
300	2,5	0,08 kg	CCA-O-7017


## Earthing Bar



**Material** Copper **Finish** PVC Jacket **Packaging** One set in a box

Length (mm)	Cross Section	Weight kg	Part No
490	2,5	0,3 kg	CCA-O-7019

## Baying Kit for inorax Series




**Material** 2 mm Galvanized Steel

**Packaging** 4 pieces in a set

H (mm)	D (mm)	W (mm)	Weight kg	Part No
23	86	52	0,125	CSA-O-7001

## Stabilizer for raised floor



**Material** 3 mm Steel **Finish** Electrostatic Powder Paint

**Set** Kit includes 4 or 6 pcs anchor sets

Raised Floor H	Cabinet D	# of Anchors	Set Weight kg	Part No
300	< 800	4	44,68	CCA-X-7010
300	> 800	6	67,02	CCA-X-7011
600	< 800	4	89,36	CCA-X-7012
600	> 800	6	134,04	CCA-X-7013

# Accessories

## Heavy Duty Castor Set



**Material** Steel and Plastic ABS **Finish** Zinc Plated

**Packaging** 2 pcs with stopper and 2 pcs without stopper in a box

Maximum Static Load	Set Weight kg	Part No
600 kg / piece	0.77	CCA-0-7016

## Castor Set



**Material** Steel and Plastic ABS **Finish** Zinc Plated

**Packaging** 2 pcs with stopper and 2 pcs without stopper in a box

Maximum Static Load	Set Weight kg	Part No
250 kg / piece	0.77	CCA-0-7015

## Adjustable Feet



**Material** Steel and Plastic ABS **Finish** Zinc Plated

**Packaging** 4 pcs in a box

Maximum Static Load	Set Weight kg	Part No
600 kg / piece	0.35	CCA-0-7014

## Cage Nut & Bolt & Plastic Cup Washer Set



**Material** Steel **Diameter** 6 mm (M6) **Finish** Zinc Plated

**One Set Includes** 20 pieces of M6x15 Screw, M6 Nut, M6 Polyamid Washer

Quantity in a set	Set Weight kg	Part No
20	0,10	CCA-0-7018

## Separator for Bayed Cabinets



**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint


**For Inorax Series**

H (mm)	D (mm)	Part No
42U	1000	CSA-X-8003
42U	1200	CSA-X-8004
47U	1000	CSA-X-8005
47U	1200	CSA-X-8006

**For Inorax-AI Series**


H (mm)	D (mm)	Part No
42U	1000	CPA-X-8003
42U	1200	CPA-X-8004
47U	1000	CPA-X-8005
47U	1200	CPA-X-8006

# Accessories



Canovate recommends to use special cable channel systems on top of the cabinets, where you don't have any raised floor or cable tray systems in your datacenters. This system is especially a very cost effective solution for datacenters with cold aisle containment systems and inrow front coolers, where you don't need a raised floor. These channel system helps to guide, route and manage any copper or fiber cable directly through the top cover inside the rack.


## Data Cable Gate Shield



**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint  
**Packaging** 1 pc in a box

W (mm)	D (mm)	H (mm)	Weight kg	Part No
500	75	125	1,50	CPA-X-6008


## Power Cable Gate



**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint  
**Packaging** 1 pc in a box

W (mm)	D (mm)	H (mm)	Weight kg	Part No
500	275	175	3,15 kg	CPA-X-6001

## Data Cable Shield with Double Side Entry



**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint  
**Packaging** 1 pc in a box

Cabinet W(mm)	W (mm)	D (mm)	H (mm)	Weight kg	Part No
600	580	100	125	1,82	CPA-X-6006
800	735	100	125	2,31	CPA-X-6007


## Data Cable Gate Shield with Double Side Entry



**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint  
**Packaging** 1 pc in a box

W (mm)	D (mm)	H (mm)	Weight kg	Part No
500	275	175	1,31	CPA-X-6009


## Data Cable Shield with One Side Entry



**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint  
**Packaging** 1 pc in a box

Cabinet W(mm)	W (mm)	D (mm)	H (mm)	Weight kg	Part No
600	580	125	100	1,87	CPA-X-6010
800	735	125	100	2,75	CPA-X-6011

## Power Cable Inlet



**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint  
**Packaging** 1 pc in a box

Cabinet W(mm)	W (mm)	D (mm)	H (mm)	Weight kg	Part No
600	580	340	185	4,84	CPA-X-6002
800	735	340	185	6,15	CPA-X-6003

## Power Cable Channel



**Material** 1,5 mm Steel **Finish** Electrostatic Powder Paint  
**Packaging** 1 pc in a box

Cabinet W(mm)	W (mm)	D (mm)	H (mm)	Weight kg	Part No
600	580	340	185	5,03	CPA-X-6004
800	735	340	185	6,35	CPA-X-6005