



VZ-PVM-I4W3 ADVANTAGES

- 32" iP Public View Monitor
- **Onvif Compliant (Fully Compatible with VMS) - Profile S**
- "A" Commercial Grade LED
- Built in 2.1 Mega Pixel Camera
- Camera Motion Sensor
- Timed Source Switching
- Auto Power / Source Recovery
- 600 TV Line - Analog Video Resolution
- PIP / PBP / VOV
- BNC(NTSC/PAL), VGA, 2 HDMI, DVI, PC Stereo
- 3D Comb-filter, De-interlace
- Support dual voltage solution (110V AC and 24V DC)
- 3-Year Warranty



MODEL # VZ-PVM-I4W3	
DISPLAY	
Screen Size	32"
Max. Resolution	1920 x 1080 @60Hz
Pixel Pitch	0.36375mm x 0.36375mm
Brightness	350cd/m²(Typical)
Contrast Ratio	3000:1
Aspect Ratio	16 : 9
Viewing Angle (H/V)	178° / 178°
Display Color	16.7 Million
Response Time	< 6.5 ms
Video System	NTSC / PAL
Frequency (H) / Frequency (V)	31 ~ 80Khz / 56 ~ 75Hz

INTERFACE	
AV (Composite) In / Out	1 / 1
Camera Out	1
DVI - In / HDMI In / VGA In (15Pin D-Sub)	1 / 2 / 1
PC Stereo In / Out	1 / 1

SPECIAL FEATURES	
Multi Display Function	PIP / PBP / VOV
Filter Type	3D Comb-filter / De-Interlace
Analog Video Resolution (MAX)	600 TV Line
Multi-lingual Language	English, Spanish, French, German, Italian, Portuguese, Dutch

DIMENSIONS & WEIGHT	
Outline Dimension (W x H x D)	28.86" x 20.52" x 3.58" 733mm x 521.2mm x 91mm
Net Weight / Gross Weight	36.82 lbs (16.7kg) / 46.3 lbs (21 kg)

MOUNT	
VESA	200mm x 200mm / M6 x 8 Screws

GENERAL			
Transmitter - IR Remote Control		YES	
Power	Electrical Ratings	AC 110~240V (50/60Hz)	24V DC
	Consumption	66W	66W
Warranty	Parts/ Labor	3 Year / 3 Year	
	MTBF (Approx.)	50,000 Hours	
Operating Temperature		32 - 104°F / 0 - 40°C	
Regulation		TUV-NRTL (=UL), FCC(A)	
Compatible Mounts	Wall	VZ-WM50, VZ-AM02	
	Ceiling	VZ-CM06, VZ-CM18, VZ-CMK01, VZ-CMK03	


CAMERA	
Camera Type	2.1 Mega Pixel IP Camera
Image Sensor	Panasonic 2.1 Mega Pixel C-MOS Sensor
Lens	DC Auto Iris 2.8~12mm Vari-focal Lens
Active Pixels	1920(H) x 1080p(V) 30fps
Video Compression	H.264, CBR, VBR support
Video Out	1ch CVBS (NTSC/PAL) / 1ch RJ-45 output
Motion Detection	Support
Ethernet Port	10 / 100 Base-T
Webclient Connection Protocol	TCP / IP
Support Protocol	IHTTP, TCP/UDP/IP, ARP, ICMP, RTP/RTSP, Multicast, Telnet, ftp, PPPoE, SMTP(e-mail), DHCP, NTP, uPNP, etc, ONVIF, PSIA support
Function	2D/3D NR, D-ZOOM, DPC, HLC/BLC, Defog D/N, DWDR, AGC, AWB, IR SMART
Dynamic IP	Dedicated dynamic IP service using www.ipcctvdns.com

MEDIA CARD - Optional Feature	
External Storage	Support SD/SDHC CARD, USB 2.0 HOST
Output	VIDEO - HDMI(1080p) / AUDIO - L/R, HDMI
VIDEO Format	RM, RMVB, AVI, DVIX, MKV, MOV, HDMOV, MP4, M4V, PMP, AVC, FLV, VOB, MPG, DAT, MPEG, TS, TP, M2TS, WMV, H.264, H.263, WMV9, VC-1, MPEG1/2/4
VIDEO Resolution	1080P @60Hz
AUDIO Format	MPEG1/2/4, MP3, WMA, OGG, AAC, FLAC, APE, AC-3, DTS, ATRA, WAV, PCM
Image Format	JPEG, TIF, PNG, BMP
VIDEO Play Control	AUTO, REPEAT, ZOOM, RESUME, TIME


Contact ViewZ

- Address : 177 W. Orangethorpe Ave., Placentia, CA 92870
- Phone : (714) 996-1177, Fax : (714) 996-1138
- Sales : sales@viewzusa.com
- Specification subject to change without notice.

DIMENSIONS



INTERFACE



1. HDMI2 IN
2. HDMI1 IN
3. VGA IN
4. DVI IN
5. PC STEREO IN/AUDIO OUT
6. CAMERA OUT
7. AV(composite)2 IN/OUT
8. IP CAMERA ETHERNET
9. MEDIA CARD(USB, SD) - Optional
10. DC 24V IN
11. AC 110~240 V IN

Contact ViewZ

- Address : 177 W. Orangethorpe Ave., Placentia, CA 92870
- Phone : (714) 996-1177, Fax : (714) 996-1138
- Sales : sales@viewzusa.com
- Specification subject to change without notice.