

Product information

GECKO 4TX

Industrial Ethernet: Lite Managed Switches: GECKO 4TX

<http://e-catalog.hirschmann.com/link/57078-24455-402707-402708/en/conf/ui/state>

Name	GECKO 4TX
	
	Lite Managed Industrial ETHERNET Rail-Switch, Ethernet/Fast-Ethernet Switch, Store and Forward Switching Mode, fanless design.
Delivery informations	
Availability	available
Product description	
Description	Lite Managed Industrial ETHERNET Rail-Switch, Ethernet/Fast-Ethernet Switch, Store and Forward Switching Mode, fanless design.
Port type and quantity	4 x 10/100BASE-TX, TP-cable, RJ45 sockets, auto-crossing, auto-negotiation, auto-polarity
Type	GECKO 4TX
Order No.	942 104-001
More interfaces	
Power supply/signaling contact	1 plug-in terminal block, 3-pin, no signaling contact
Network size - length of cable	
Twisted pair (TP)	0 m ... 100 m
Network size - cascability	
Line - / star topology	any
Power requirements	
Operating voltage	DC 9.6 V - 32 V
Current consumption at 24 V DC	120 mA
Power consumption	2,9 W
Software	
Management	Web-interface, HTTP(s) config file/firmware transfer, SNMP v1/v2/v3
Diagnostics	Device status indication (LEDs), Log-File, RMON (1) statistics, Simple interface statistics, Topology Discovery according to IEEE 802.1AB (LLDP)
Configuration	BOOTP/DHCP, DHCP Option 82, HiDiscovery
Security	SNMPv3 (authNoPriv), Possibility to disable each port
Redundancy functions	RSTP (IEEE 802.1D-2004)
Filter	TOS/DSCP prioritization (Mapping TOS/DSCP to 802.1D/p), Prioritization through 4 queues, Static unicast/multicast filter entries (up to 100)
Ambient conditions	
Operating temperature	0 °C ... 60 °C
Storage/transport temperature	-40 °C ... 85 °C
Relative humidity (non-condensing)	5 % ... 95 %
MTBF	23 years
Mechanical construction	
Dimensions (W x H x D)	25 mm x 114 mm x 79 mm
Mounting	DIN Rail
Weight	100 g
Protection class	IP30
Mechanical stability	
IEC 60068-2-27 shock	15 g, 11 ms duration, 18 shocks
IEC 60068-2-6 vibration	3.5 mm, 5-8.4 Hz, 10 cycles, 1 octave/min; 1 g, 8.4-150 Hz, 10 cycles, 1 octave/min
EMC interference immunity	
EN 61000-4-2 electrostatic discharge (ESD)	4 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field	10 V/m (80-3000 MHz)
EN 61000-4-4 fast transients (burst)	2 kV power line, 4 kV data line
EN 61000-4-5 surge voltage	power line: 2 kV (line/earth), 1 kV (line/line), 2 kV data line IEC61131: power line 5 kV (line/earth)
EN 61000-4-6 conducted immunity	10 V (150 kHz-80 MHz)

Industrial Ethernet:Lite Managed Switches:GECKO 4TX
<http://e-catalog.hirschmann.com/link/57078-24455-402707-402708/en/conf/ui/istate>
EMC emitted immunity
FCC CFR47 Part 15 FCC 47 CFR Part 15 Class A

EN 55022 EN 55022 Class A

Approvals
Safety of industrial control equipment UL61010-1/-2-201 (pending)

Scope of delivery and accessories
Scope of delivery Device, terminal block, operating manual

Accessories to order separately Rail power supply RPS 30, RPS 80 EEC or RPS 120 EEC (CC)

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

 E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.