


DB
RATED

One-Hole Grounding Lay-In Lug

- Used for quick installation of a continuous grounding conductor
- UL 467 Listed for grounding and bonding, copper lugs
UL Listed for direct burial in earth or concrete

- UL Listed for use up to 600 V and temperature rated 90°C
- Wide wire range-taking capability minimizes inventory requirements



Copper



Tin-Plated Copper



Aluminum

Part Number	Set Screw Material	Conductor Size Range	Stud Hole Size In.	Hex Key Size In.	Length In.	Width In.	Height In.	Std. Pkg. Qty.
-------------	--------------------	----------------------	--------------------	------------------	------------	-----------	------------	----------------

Copper Body

LICC4-22-C	Stainless Steel	#14 AWG – #4 AWG	0.22	**	1.09	0.39	0.75	100
-------------------	-----------------	------------------	------	----	------	------	------	-----

Tin-Plated Copper Body

LICC4-22TP-C	Stainless Steel	#14 AWG – #4 AWG	0.22	**	1.09	0.39	0.75	100
---------------------	-----------------	------------------	------	----	------	------	------	-----

Tin-Plated Aluminum Body

LIAC4-22-C	Stainless Steel	#14 AWG – #4 AWG	0.22	**	1.06	0.39	0.78	100
LIAS1/0-14-L	Zinc Plated Steel	#14 AWG – 1/0 AWG	0.27	**	1.50	0.61	1.10	50
LIAS250-56-Q	Zinc Plated Steel	#6 AWG – 250 kcmil	0.33	1/4	2.20	0.80	1.70	25

**Uses slotted head set screw.

The use of Panduit oxide inhibiting joint compound (CMP) is recommended for pad to conductor connections. Refer to www.panduit.com for more information.